







P	LTR	DESCRIPTION	DATE	DWN	APVD
	51	Initial Version	01JUN2010	APER	-
	A	Initial Release	25NOV2013	APER	-
	B	Marking Correction	26FEB2024	GL	-



NOTES

- 1 Datecode as ++YYWW (Year and Week), for traceability.
- 2 Cover marking (Printed, Moulded or Lasered) includes:
TE Logo and Part Alias, Nominal values and Circuit Diagram.
- 3 Sealed area with Epoxy (IP67)
- 4 Sealed area with Epoxy (Electrical isolation)
- 5 Coil Connection:
Connector AMP Superseal 1.5 series PN 282080-1
- 6 Load Connection:
Cable lug M6, maximum cable section 25 mm²
- 7 Maximum torsion of screw bolts: 5Nm
Higher tightening torques could be applied depending on
the used nuts. Needs to be agreed between TE and the
customer.

CIRCUIT DIAGRAM



RELAY TE PN	TE PART ALIAS	REV.
1-1414476-0	V23132-A2001-X023	0

THIS DRAWING IS A CONTROL DOCUMENT.		DWN G. Lopes	26FEB2024		TE Connectivity	
DIMENSIONS: mm		CHK S. Baptista	26FEB2024		TE	
TOLERANCES UNLESS OTHERWISE SPECIFIED: ISO 8015		APVD	-	NAME	HCR150 Normally Open 12V	
0 PLC ±0.1 1 PLC ±0.1 2 PLC ±0.001 3 PLC ±0.001 4 PLC ±0.0001		PRODUCT SPEC	-			
ANGLES		APPLICATION SPEC	-	SIZE	CAGE CODE	DRAWING NO
MATERIAL		WEIGHT	-	A2	00779	G-V23132-A2001-X023
FINISH						RESTRICTED TO
						-
CUSTOMER DRAWING				SCALE	1:1	SHEET 1 OF 1
						REV B