









P.C. LAYOUT



CIRCUIT: SPST ▲

## NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=± 0.4  
X.XX=± 0.25
3. TERM. NUMBERS FOR REF. ONLY.
4. RATING: 50mA @ 12VDC
- ▲ 5. OPERATING FORCE: 100± 50gf
6. TRAVEL: 0.25 +0.2/-0.1mm
7. CONTACT RESISTANCE: 100 mΩ MAX.
- ▲ 8. CONTACT MATERIAL: SILVER
9. DIELECTRIC STRENGTH: 250V RMS min.
10. INSULATION RESISTANCE: 100 MEGAΩ min.
11. ELECTRICAL LIFE: 100,000 CYCLES
12. ▲ DENOTES CRITICAL PARAMETER.
13. OPERATING TEMP: -40°C TO 85°C
14. PACKAGE: POLYBAG/ 750 PIECES PER BAG



E-SWITCH®

|     |        |                              |          |     |
|-----|--------|------------------------------|----------|-----|
| B   | 24520  | CHANGE OPERATING TEMPERATURE | 10/6/20  | JM  |
| A   | 20812  | RELEASED FOR PRODUCTION      | 10/10/12 | EBP |
| REV | PCR NO | DESCRIPTION                  | DATE     | BY  |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY  
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE TLE1105F100Q

SCALE  
4:1DATE  
10/10/2012DR  
EBPDWG  
P010114REV  
B