

Flat Cable EMI Suppression Cores (2643180851)



Part Number: 2643180851

43 SPLIT FLAT CABLE CORE

Explanation of Part Numbers:

- Digits 1 & 2 = Product Class
- Digits 3 & 4 = Material Grade

Flat cable suppression core can accommodate multi- conductors flat cables, in widths from 12.7 mm (0.500) up to 77 mm (3.0). These flat cable cores are available in two ferrite material grades to reduce conducted EMI from 1 MHz to hundreds of MHz.

Our Expanded Cable & Suppressor Kit (part number 0199000005) contains a selection of these flat cable cores and clips.

Flat Cable Cores are available in selected sizes in the Flex Circuit & Ribbon Cable Core Kit (part number 0199000038).

Assembly clips are available for most of the split flat cable cores. See section Flat Cable Cores Assembly clips.

[Catalog Drawing](#)

[3D Model](#)

Weight: 1.3 (g)

Dim	mm	mm tol	nominal inch	inch misc.
A	12.8	±0.40	0.504	—
B	9.8	±0.25	0.386	—
C	12	±0.40	0.472	—
D	2.1	±0.20	0.083	—
E	0.5	±0.1	0.02	—

Cable Information			
Max Diameter	Max Dimension	Solid Equivalent	Flat Cable Cores
0.0	9.50 x 0.80	—	—




Chart Legend

+ Test frequency


•For assembly clips see Flat Cable Cores Assembly Clips

Typical Impedance (Ω)	
10 MHz	23
25 MHz ⁺	38
100 MHz ⁺	63
250 MHz	90

Flat cable suppression cores, split or single cores, are controlled for impedances only. Minimum impedance values are specified for the + marked frequencies. The minimum impedance is listed on our catalog drawing.

[Catalog Drawing](#)

Centered, single turn impedance tests for the 31 and 43 material parts are performed on the E4990A Impedance Analyzer. All tests are made with the shortest practical wire length.



[CSV Download](#)