









X	H
A	4.3
A1	4.5
A2	4.8
B	5.0
B1	5.3
B2	5.5
C	6.0



SPECIFICATION

Contact Rating:	50mA,12V DC
Contact Resistance:	100mΩ max
Insulation Resistance:	100mΩ min.500V DC
Dielectric Strength:	250V AC/1minute
Travel:	0.20mm
Operating Temp:	-20℃~+70℃
Storage Temp:	-30℃~+80℃

PAPT NO	TC-1101V-X-X-X
Operating Force	A:100gf B:160gf C:260gf
Height	Code-X
Color	B:black W:white



⑤	Terminal	—	2	Brass (0.30t)	Plating silvering	—
④	Contact	—	1	F.ag/Sus	Natural	—
③	Base	—	1	PPA		—
②	Cover	—	1	Spcc	Plating Nickel	—
①	Keystake	—	1	PPA		—
ITEM	PAPT NAMF	TER.NO	QTY	MATERIAL	FINISHING	REMARK

PCB-WELDING-DRAWING

CIRCUIT DIAGRAM

DSND		SCALE: N/A	MODEL TYPE:
DWN		VIEW:	PART NO.: TC-1101V-X-X-X
CHKD		UNIT: mm/in	DWG NO.:
APPD		SIZE: A4	
WEIGHT		SHEET	REVISIC
		1/1	A0

XKLB

XKB INDUSTRIAL PRECISION CO.,LIMITED

广东星坤科技股份有限公司

ΔX	日期
ΔX	日期
ΔX	日期
MARK	DESCRIPTION

文件工程章

REVISIONS
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn

ANGLAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5
UNSPECIFIED TOLERANCES	