




VER	Description	ECN	Name	Date
A	Initial Released	N/A	Patrick	2018/10/20



I. MATERIALS & FINISHES

Component	Material	Finishes	Thk. (u")
Body	Brass	Sn-Ni	100
Contact Pin	Beryllium Copper	Gold	50
Insulator	PTFE	--	--
Coupling Nut	Brass	Sn-Ni	100
Ferrule	Brass	Sn-Ni	100
Gasket	Silicone Rubber	--	--

II. ELECTRICAL PROPERTIES

Impedance (Ω):	50
Frequency Range (GHz):	DC-8 GHz
Dielectric Withstanding Voltage (V r.m.s):	2000
Insulation Resistance (M Ω):	≥ 5000
VSWR:	≤ 1.30 (DC-6 GHz)
	≤ 1.40 (6-8 GHz)
Insertion Loss (dB, f / GHz):	-0.1 x sqrt (f)

III. ENVIRONMENT PROPERTIES


Temperature Range:	-40°C ~ +125°C
Thermal Shock:	MIL-STD-202, Meth. 107, Cond. B
Vibration:	MIL-STD-202, Meth. 204, Cond. B
Shock:	MIL-STD-202, Meth. 213, Cond. G
Climatic Class:	IEC 60068 55/155/21
RoHS:	Compliant

IV. MECHANICAL PROPERTIES

Center Conductor:	Spring Finger
Outer Conductor:	Crimp
Coupling Nut Torque (in-lbs):	6-10
Cable-Connector Retention Force (lbs):	90
Durability (Cycles):	500

V. Tooling & Accessories

Stripping Tool: 3192-084/CST-300
Crimping Tool: 3190-666/CT-400/300
Heat Shrink Tube: 1/2"x1.5" (3:1) 1 pcs



RECOMMENDED CABLE STRIPPING DIM'S
Connector Adds: 15.95 mm

Compatible with Standard: IEC 61169-16

UNLESS OTHERWISE SPECIFIED						DFTM Patrick		TIMES MICROWAVE SYSTEMS An Amphenol Company EZ-300-NMH-RA-X Type N Male (Plug) Right Angle Non-Solder Pin No Braid Trim Connector for LMR-300 Cable			
ALL DIMENSIONS ARE IN mm MACHINED SURFACES FINISH 1.6 RMS MAX. REMOVE ALL BURRS 0.15X45° MAX. BREAK MACHINE CORNERS 0.15X45° D MAX. FILLET R. TOLERANCES ON DECIMALS .X ±0.1 .XX ±0.15 ANGLES ±2° FRACTIONS ± N/A						DATE 2018/10/20					
						CHKD Monica					
						DATE 2018/10/20					
						APPD Joslen					
Scale: 3:1		Size: A3		CODE IDENT 68999		DATE 2018/10/20		SHT 1/1	3190-8012		REV A