







REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



RECOMMENDED PCB LAYOUT
RECOMMENDED PCB THICKNESS: 1.6mm.
TOLERANCE: ±0.05 (TOP VIEW)

- NOTE:
- MATERIAL:
 - HOUSING: PA9T, WITH 30% GF, UL94 V-0, BLACK COLOR.
 - INSERT HOUSING: PA9T, WITH 30% GF, UL94 V-0, BLACK COLOR.
 - PICK CAP: PA46, WITH 30% GF, UL94 V-0, BLACK COLOR.
 - CONTACTS: PHOSPHOR BRONZE.
 - HOLD DOWN: BRASS.
 - FINISH:
 - CONTACTS: (SEE TABLE) GOLD PLATED ON CONTACT AREA, GOLD FLASH ON SOLDER TAIL, 1.27um [50u"] MIN. NICKEL UNDERPLATED OVERALL.
 - HOLD DOWN: 2.54um [100u"] MIN. MATTE TIN PLATED.
 - REFLOW SOLDER CAPABLE TO 260°C PER TEC-109-201, CONDITION B.
- 4** OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

4 OBSOLETE	8P8C	WITH	1.27µm [50µ"]	2-1734858-8
			0.76µm [30µ"]	2-1734858-7
			0.38µm [15µ"]	2-1734858-6
			0.15µm [6µ"]	2-1734858-5
4 OBSOLETE	8P8C	WITHOUT	1.27µm [50µ"]	2-1734858-4
			0.76µm [30µ"]	2-1334858-3
			0.38µm [15µ"]	2-1734858-2
			0.15µm [6µ"]	2-1734858-1
	RJ45	PICK CAP	MIN.GOLD THICKNESS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN O. HU 06NOV2007	TE Connectivity		
		CHK S. HOU 06NOV2007			
		APVD W. KODAMA 06NOV2007	NAME		
DIMENSIONS: mm		PRODUCT SPEC 108-57464	MODULAR JACK RJ45/RJ11 TOP ENTRY, SMT TYPE		
		APPLICATION SPEC —	—		
MATERIAL SEE NOTE		WEIGHT 3.3	SIZE A3	CAGE CODE 00779	DRAWING NO C-1734858
		FINISH SEE NOTE	SCALE 1:1	SHEET 2 of 3	REV B
CUSTOMER DRAWING					

