








Recommended P.C.B layout



SPECIFICATION

Contact Rating:	50mA, 12V DC
Contact Resistance:	100mΩ max
Insulation Resistance:	100mΩ min. 500V DC
Dielectric Strength:	250V AC/1minute
Travel:	0.25mm
Operating Temp:	-30℃~+85℃
Storage Temp:	-30℃~+80℃

PAPT NO	TS-1102T-X
Operating Force	A:100gf B:160gf C:260gf
Height	D:7.3

⑤	Terminal	—	4	Brass (0.30t)	Plating silvering	—
④	Contact	—	1	F.ag/Sus	Natural	—
③	Base	—	1	Pa46		—
②	Cover	—	1	Spcc	Plating Nickel	—
①	Keystake	—	1	Pa46		—
ITEM	PAPT NAMF	TER.NO	QTY	MATERIAL	FINISHING	REMARK

DSND		SCALE: N/A	MODEL TYPE: TACT SWITCH		
DWN		VIEW: 	PART NO.: TS-1102T-X		
CHKD		UNIT: mm/in	DWG NO.:		
APPD		SIZE: A4			
PRECISION CO., LIMITED			WEIGHT	SHEET	REVISI
				1/1	A0

广东星坤科技股份有限公司				3						ANGLAR		±5°	
ΔX		日									L ≤ 4	±0.2	
ΔX		期									4 < L ≤ 16	±0.3	
ΔX											16 < L ≤ 63	±0.4	
MARK		DESCRIPTION		DATE	REVISED	APPROVED					L > 63	±0.5	
零件工程章											UNSPECIFIED TOLERANCES		
www.helloxb.com www.helloxb.cn www.xk-da.cn													

XKLE

XKB INDUSTRIAL PRECISION CO.,LIMITED