



P	LTR	DESCRIPTION	DATE	DWN	APVD
	A2	PART STATUS UPDATED	23JAN2018	RK	PS



		1 MATERIALS AND FINISH HOUSING: PA 6-6, UL 94-V0, COLOR: GRAY. TERMINAL: COPPER ALLOY, TIN PLATED. 2 SUITABLE FOR 1,6-2,4mm PC BOARD THICKNESS. 3 END-TO-END STACKABLE WITHOUT LOSS OF CENTERLINE SPACING. 4 RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORIES INC.FILE N° E60677. 5 IMQ CERTIFICATE WITH SURVEILLANCE IN CONFORMITY WITH IEC 998-1/998-2-1. 6 NOT CUMULATIVE TOLERANCE. 7 BUCHANAN LOGO TO APPEAR ON HOUSING, LOCATION OPTIONAL WHERE SPACE PERMITS.	<table> <tr><td data-bbox="2208 1016 2368 1491" rowspan="13">OBSOLETE</td><td data-bbox="2368 1016 2528 1035">127.00</td><td data-bbox="2528 1016 2659 1035">25</td><td data-bbox="2659 1016 2893 1035">2-1546110-5</td></tr> <tr><td data-bbox="2368 1035 2528 1054">121.92</td><td data-bbox="2528 1035 2659 1054">24</td><td data-bbox="2659 1035 2893 1054">2-1546110-4</td></tr> <tr><td data-bbox="2368 1054 2528 1071">116.84</td><td data-bbox="2528 1054 2659 1071">23</td><td data-bbox="2659 1054 2893 1071">2-1546110-3</td></tr> <tr><td data-bbox="2368 1071 2528 1089">111.76</td><td data-bbox="2528 1071 2659 1089">22</td><td data-bbox="2659 1071 2893 1089">2-1546110-2</td></tr> <tr><td data-bbox="2368 1089 2528 1106">106.68</td><td data-bbox="2528 1089 2659 1106">21</td><td data-bbox="2659 1089 2893 1106">2-1546110-1</td></tr> <tr><td data-bbox="2368 1106 2528 1125">101.60</td><td data-bbox="2528 1106 2659 1125">20</td><td data-bbox="2659 1106 2893 1125">2-1546110-0</td></tr> <tr><td data-bbox="2368 1125 2528 1144">96.52</td><td data-bbox="2528 1125 2659 1144">19</td><td data-bbox="2659 1125 2893 1144">1-1546110-9</td></tr> <tr><td data-bbox="2368 1144 2528 1161">91.44</td><td data-bbox="2528 1144 2659 1161">18</td><td data-bbox="2659 1144 2893 1161">1-1546110-8</td></tr> <tr><td data-bbox="2368 1161 2528 1180">86.36</td><td data-bbox="2528 1161 2659 1180">17</td><td data-bbox="2659 1161 2893 1180">1-1546110-7</td></tr> <tr><td data-bbox="2368 1180 2528 1199">81.28</td><td data-bbox="2528 1180 2659 1199">16</td><td data-bbox="2659 1180 2893 1199">1-1546110-6</td></tr> <tr><td data-bbox="2368 1199 2528 1215">76.20</td><td data-bbox="2528 1199 2659 1215">15</td><td data-bbox="2659 1199 2893 1215">1-1546110-5</td></tr> <tr><td data-bbox="2368 1215 2528 1234">71.12</td><td data-bbox="2528 1215 2659 1234">14</td><td data-bbox="2659 1215 2893 1234">1-1546110-4</td></tr> <tr><td data-bbox="2368 1234 2528 1251">66.04</td><td data-bbox="2528 1234 2659 1251">13</td><td data-bbox="2659 1234 2893 1251">1-1546110-3</td></tr> <tr><td data-bbox="2208 1251 2368 1491" rowspan="8">OBSOLETE</td><td data-bbox="2368 1251 2528 1270">60.96</td><td data-bbox="2528 1251 2659 1270">12</td><td data-bbox="2659 1251 2893 1270">1-1546110-2</td></tr> <tr><td data-bbox="2368 1270 2528 1289">55.88</td><td data-bbox="2528 1270 2659 1289">11</td><td data-bbox="2659 1270 2893 1289">1-1546110-1</td></tr> <tr><td data-bbox="2368 1289 2528 1306">50.80</td><td data-bbox="2528 1289 2659 1306">10</td><td data-bbox="2659 1289 2893 1306">1-1546110-0</td></tr> <tr><td data-bbox="2368 1306 2528 1325">45.72</td><td data-bbox="2528 1306 2659 1325">9</td><td data-bbox="2659 1306 2893 1325">1546110-9</td></tr> <tr><td data-bbox="2368 1325 2528 1344">40.64</td><td data-bbox="2528 1325 2659 1344">8</td><td data-bbox="2659 1325 2893 1344">1546110-8</td></tr> <tr><td data-bbox="2368 1344 2528 1360">35.56</td><td data-bbox="2528 1344 2659 1360">7</td><td data-bbox="2659 1344 2893 1360">1546110-7</td></tr> <tr><td data-bbox="2368 1360 2528 1379">30.48</td><td data-bbox="2528 1360 2659 1379">6</td><td data-bbox="2659 1360 2893 1379">1546110-6</td></tr> <tr><td data-bbox="2368 1379 2528 1398">25.40</td><td data-bbox="2528 1379 2659 1398">5</td><td data-bbox="2659 1379 2893 1398">1546110-5</td></tr> <tr><td data-bbox="2368 1398 2528 1415">20.32</td><td data-bbox="2528 1398 2659 1415">4</td><td data-bbox="2659 1398 2893 1415">1546110-4</td></tr> <tr><td data-bbox="2368 1415 2528 1434">15.24</td><td data-bbox="2528 1415 2659 1434">3</td><td data-bbox="2659 1415 2893 1434">1546110-3</td></tr> <tr><td data-bbox="2368 1434 2528 1451">10.16</td><td data-bbox="2528 1434 2659 1451">2</td><td data-bbox="2659 1434 2893 1451">1546110-2</td></tr> <tr><td data-bbox="2368 1451 2528 1491"></td><td data-bbox="2528 1451 2659 1491">NO OF POSN</td><td data-bbox="2659 1451 2893 1491">PART NUMBER</td></tr> </table>	OBSOLETE	127.00	25	2-1546110-5	121.92	24	2-1546110-4	116.84	23	2-1546110-3	111.76	22	2-1546110-2	106.68	21	2-1546110-1	101.60	20	2-1546110-0	96.52	19	1-1546110-9	91.44	18	1-1546110-8	86.36	17	1-1546110-7	81.28	16	1-1546110-6	76.20	15	1-1546110-5	71.12	14	1-1546110-4	66.04	13	1-1546110-3	OBSOLETE	60.96	12	1-1546110-2	55.88	11	1-1546110-1	50.80	10	1-1546110-0	45.72	9	1546110-9	40.64	8	1546110-8	35.56	7	1546110-7	30.48	6	1546110-6	25.40	5	1546110-5	20.32	4	1546110-4	15.24	3	1546110-3	10.16	2	1546110-2		NO OF POSN	PART NUMBER
	OBSOLETE	127.00	25		2-1546110-5																																																																											
121.92		24	2-1546110-4																																																																													
116.84		23	2-1546110-3																																																																													
111.76		22	2-1546110-2																																																																													
106.68		21	2-1546110-1																																																																													
101.60		20	2-1546110-0																																																																													
96.52		19	1-1546110-9																																																																													
91.44		18	1-1546110-8																																																																													
86.36		17	1-1546110-7																																																																													
81.28		16	1-1546110-6																																																																													
76.20		15	1-1546110-5																																																																													
71.12		14	1-1546110-4																																																																													
66.04		13	1-1546110-3																																																																													
OBSOLETE	60.96	12	1-1546110-2																																																																													
	55.88	11	1-1546110-1																																																																													
	50.80	10	1-1546110-0																																																																													
	45.72	9	1546110-9																																																																													
	40.64	8	1546110-8																																																																													
	35.56	7	1546110-7																																																																													
	30.48	6	1546110-6																																																																													
	25.40	5	1546110-5																																																																													
20.32	4	1546110-4																																																																														
15.24	3	1546110-3																																																																														
10.16	2	1546110-2																																																																														
	NO OF POSN	PART NUMBER																																																																														

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±.2

1 PLC ±.25

2 PLC ±.25

3 PLC ±.25

4 PLC ±.25

ANGLES ±2

FINISH

MATERIAL

DWN S. WELDON 11SEP2002

CHK C. RICHARD 11SEP2002

APVD C. RICHARD 11SEP2002

PRODUCT SPEC 108-20166

APPLICATION SPEC 114-20079

WEIGHT -

CUSTOMER DRAWING

NAME

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

SCALE

SHEET

OF

REV

A2

TE Connectivity

TERMINAL BLOCK HEADER ASSEMBLY

90 DEGREE, OPEN ENDS, STACKING

5.08mm PITCH

C-1546110

A2