



Connectors > Circular Connectors > Standard Circular Connectors



Connector System: **Wire-to-Wire**
Number of Positions: **74**
Sealable: **Yes**
Connector & Contact Terminates To: **Wire & Cable**
Contact Current Rating (Max): **7.5 A**

Features

Product Type Features

Product Type	Connector
Assembly Type	Electrical Connector
Connector System	Wire-to-Wire
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
Circular Connector Type	Receptacle
Shell Type	Square Flange Receptacle

Configuration Features

Keying & Polarized Position Locations	2
Factory Installed Backshell	No
Keying	Key Polarization 2
Number of Positions	74
Number of Power Positions	74
Number of Signal Positions	74
Contacts Preloaded	No

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------



Voltage	1800 Vrms
---------	-----------

Body Features

Peripheral Seal Material	Silicone
Environmental Protection	Yes
Feedthrough Type	No
O-Ring Material	Silicone
Environmental Protection Type	Elastomer Sealed
Entry Style	Rear Insertion
Fluid Type	Coolanol 25, M2-V, MIL-DTL-5624 (JP-5), MIL-PRF-23699, MIL-PRF-5606, MIL-PRF-7808, SEA-AMS1424 Type I
Shell Plating Material	Tin
Shell Base Material	Composite
Circular Connector Insulation Material Type	Hard Dielectric/Silicone
Hermetically Sealed	No

Contact Features

Contact Quantity (Size 20)	74
Contact Current Rating (Max)	7.5 A
Reverse Gender	No
Contact Layout Arrangement	U74 (24-74)
Circular Connector Contact Type	Socket

Mechanical Attachment

Mating Retention Type	Bayonet
Panel Mount Feature	With
Panel Mount Feature Type	Square Flange
Connector Mounting Type	Panel Mount
Polarization Code	2
Mating Alignment Type	Keyed
Mating Retention	With

Housing Features

Circular Connector Shell Size	24
Alignment Keyed	Clocking

Dimensions

--	--



Panel Thickness	7.94 mm[.313 in]
Accepts Wire Insulation Diameter Range	1.02 – 1.88 mm[.04 – .074 in]
Assembly Length	34.19 mm[1.346 in]
Wire Size	.2 – .52 mm ²

Usage Conditions

Fluid Resistance	Yes
Operating Temperature Range	-65 – 175 °C[-85 – 347 °F]

Operation/Application

Durability Rating	1500 Cycles
Circuit Application	Power & Signal
Shielded	Yes

Packaging Features

Packaging Quantity	1
--------------------	---

Other

Position Locations Omitted	All
----------------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2021 (219) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (1.2% in Contact Lead-Copper Alloy) Decamethylcyclopentasiloxane (D5) (5% in Insert Subassembly) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as




EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CJ2087-000
[HL2010E-KIT-120V](#)



TE Part # M15570-20
[TOOL INS/REM](#)

Customers Also Bought



TE Part #1617807-5
[FC-335-SY8= RELAY, 3PST](#)



TE Part #ZPF000000000001261
[097-0267-16 A1267](#)




TE Part #1617147-5
[JMGAP-26P = M39016/17-030P](#)



TE Part #ZPF000000000007174
[983-0RS 08-98 PN](#)




TE Part #1616058-6
[A703CD \(FAA/PMA\)=RELAY](#)



TE Part #YA56-14-15SWC019
[PLUG ASSY](#)




TE Part #CX1369-000
[BSTS-13X4FR/NM](#)



TE Part #YDTS20Y13-98XNV001
[HERM RECP](#)



TE Part #1617119-5
[J1MAW-18XP = M39016/7-021P](#)



TE Part #CS8624-000
[BSTS-15X4FR/NM](#)



Documents

Product Drawings

RECP ASSY

English

Datasheets & Catalog Pages

DEUTSCH MIL-DTL-38999 CIRCULAR CONNECTORS

English