


PANEL CUTOUT




PANEL THICKNESS	(x)
0.75 - 1.25	30.0
1.25 - 2.00	30.2
2.00 - 3.00	30.5

SWITCH FUNCTION	
POS. 1	POS. 2
OFF	ON
OFF	2-1, 5-4



NOTE:

- DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
- TERMINAL NUMBERS FOR REF ONLY
- CONTACT MATERIAL: SILVER
- CONTACT RATINGS: ANSI/UL 61058-1
16A @ 125/250VAC [cURus]
20A @ 125VAC [cURus]
1/3HP 125/250VAC [cURus]
3/4HP 125/250VAC [cURus]
- CONTACT RESISTANCE: 20mΩ MAX. INITIAL
- INSULATION RESISTANCE: 100MΩ MIN. @ 500VDC
- DIELECTRIC STRENGTH: 1,000VAC FOR 1 MINUTE
- ELECTRICAL LIFE: 6,000 CYCLES [cURus]
- OPERATING TEMPERATURE: -20°C TO 65°C
- ▲ DENOTES CRITICAL PARAMETER
- ILLUMINATION: NEON LAMP
- ILLUMINATION VOLTAGE: 250V



REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
D	ECO-102065	ACTUATOR DIM 19.0 WAS 19.2	07/10/23	JS	TITLE RB242D1011-127				000000300
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					SCALE 1:1	DATE 7/27/2010	DR CAB	DWG 14-RB242D1011127	REV D