



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	ECR-19-014657	13DEC2020	RR	SZ





- 1 MATERIAL: HOUSING — NYLON, COLOR: BLACK, UL 94V-0.
OVERMOLDED TERMINAL ARRAY — PBT, COLOR: BROWN.
TERMINALS — 0.33 [.013] THICK PHOS BRONZE
PLATED WITH 1.27 μm [.000050] MINIMUM THICK
HARD GOLD IN LOCALIZED AREA AND 3.81 μm
[.000150] MINIMUM THICK MATTE TIN IN SOLDER
AREA OVER 1.27 μm [.000050] MINIMUM THICK
NICKEL UNDERPLATE.

2 JACK CAVITY CONFORMS TO FCC RULES AND
REGULATIONS, PART 68 SUBPART F.

3 USE #30 DRILL BIT OR 3.25mm DRILL BIT WHEN
PRODUCING THESE PCB HOLES.

4 CONTACT AREA LUBRICATED WITH BELLCORE APPROVED
LUBRICANT. TECHNICAL REFERENCE GR-1217-CORE,
ISSUE 1, NOVEMBER 1995



RECOMMENDED PANEL CUTOUT
SCALE 4:1

RECOMMENDED PC BOARD LAYOUT
COMPONENT SIDE
SCALE 4:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TERRY.YU 03MAR2009	TE Connectivity			
		CHK MARTIN.LI 03MAR2009				
		APVD STEVEN.YAO 03MAR2009	NAME			
		PRODUCT SPEC 108-1163-2	MODULAR JACK ASSEMBLY, SINGLE PORT, 8 POSITION, UNSHIELDED, CATEGORY 5e			
		APPLICATION SPEC 114-2048	SIZE A2	CAGE CODE 00779	DRAWING NO C=1932326	RESTRICTED TO —
MATERIAL SEE NOTE 1		FINISH SEE NOTE 1	WEIGHT 0.000000	SCALE 2:1	SHEET 1 OF 1	REV A1
		CUSTOMER DRAWING				