

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

© COPYRIGHT — TE Connectivity

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D	REVISED PER ECO-17-004099	30AUG2017	RS	DR
	E	REVISED PER ECO-18-004162	06APR2018	RS	DR

AMP WIRE RANGE	 E13288 Listed
1/0 AWG SOLID OR STRANDED	1/0 AWG STRANDED ONLY

 LR7189 Certified
1/0 AWG SOLID OR STRANDED


- 1

COPPER PER ASTM B-152, ANNEALED
- 2


TIN PLATE .000100 MIN EXT. THK PER ASTM B-545
- 3

BODY MATERIAL THK IS
1.778±0.076[.070±.003]
- 4

STAMP AMP 1/0 W* APPROX AS SHOWN



50	LOOSE PIECE	322291
QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN jr ruth 07MAY04	 TE Connectivity Ltd.		
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	MAX RECOMMENDED OPERATING TEMPERATURE: 170°C [338°F] MAX	DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK MJ SPICER 07MAY04			
				0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.127[.005] 4 PLC ± - ± 5° ANGLES FINISH	APVD MJ SPICER 07MAY04	NAME WIRE TERMINAL SOLISTRAND, RING TONGUE WIRE SIZE 1/0 AWG		
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	VOLTAGE RATING: NOT APPLICABLE			PRODUCT SPEC UL 486 A-B			
FOR ORDER ENTRY	1-800-526-5142	WIRE CROSS SECTIONAL AREA RANGE, 42.4-60.6mm²[83,700-119,500]	MATERIAL 1	FINISH 2	APPLICATION SPEC —	SIZE A3	CAGE CODE 00779	DRAWING NO C-322291
CUSTOMER DRAWING					WEIGHT	RESTRICTED TO —		REV E
					SCALE 2:1	SHEET 1 OF 1		