




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REVISED PER OG3B-0119-01	01FEB2002	EZ	DB
	C	PACKAGING CHANGE FROM BOX TO TRAY	08SEP2017	FP	NG

D




P/N 284392-2 AS SHOWN

C

C

CLAMPING SCREW


TEST FACILITY



- 1 MATERIALS AND FINISH
HOUSING : PA 6.6, UL 94-V0, COLOR GREEN.
CLAMP : BRASS, NICKEL PLATED
TERMINAL : BRASS, TIN PLATED
CLAMPING SCREW : M3, BRASS, NICKEL PLATED
2. SUITABLE FOR 1.6-2.4 mm. PC BOARD THICKNESS.
3. END-TO-END STACKABLE W/INTERLOCK WITHOUT LOSS OF CENTERLINE SPACING
4. WIRE SIZE RANGE
14 - 30 AWG

5 NOT CUMULATIVE TOLERANCE

RECOMMENDED PC BOARD LAYOUT



B

B

A

A

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN E. ZANOLINI 01FEB2002	TE Connectivity NAME TERMINAL BLOCK, PCB MOUNT, STRAIGHT SIDE ENTRY WIRE, STACKING W/ INTERLOCK, 3.81mm PITCH SIZE A3 CAGE CODE 00779 DRAWING NO C-284392 RESTRICTED TO -		
DIMENSIONS: mm		CHK E. ZANOLINI 01FEB2002			
		APVD D. BIEVENOUR 01FEB2002			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC 108-20166			
0 PLC ±0.3 1 PLC ±0.25 2 PLC ±0.25 3 PLC ±0.25 4 PLC ±0.25 ANGLES ±2°		APPLICATION SPEC 114-20079			
MATERIAL 1		FINISH 1	WEIGHT -		
CUSTOMER DRAWING			SCALE 4:1	SHEET 1 OF 1	REV C