







SWITCH FUNCTION		
POS. 1	POS. 2	POS. 3
ON	N/A	ON
2-3, 5-6	N/A	2-1, 5-4



NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NUMBERS FOR REF ONLY
- ▲ 4. PLATING MATERIAL: GOLD
5. RATING: 0.4 (VA) MAX @ 20V MAX
6. LIFE EXPECTANCY: 40,000 make-and-break cycles at full load
7. INSULATION RESISTANCE: 1,000 mILLI-OHMS min.
8. CONTACT RESISTANCE: 10 mILLI-OHMS MAX.
9. DIELECTRIC STRENGTH: 1,000 V RMS @ sea level.
10. OPERATING TEMP.: -30°C to 85°C
11. ▲ DENOTES CRITICAL PARAMETER.



A	24319	RELEASED FOR PRODUCTION	5/21/20	MW
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE 100DP1T2B1M6RE

SCALE
2:1DATE
5/21/2020DR
MWDWG
T121153REV
A