

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

C

COPYRIGHT

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

A2

REVISED (ECR-13-001312)

24JAN13

JL

WK

NOTE:

1. MATERIAL:

HOUSING: LCP WITH 30% GF, UL 94V-0, NATURE COLOR.
 SPACER: LCP WITH 30% GF, UL 94V-0, NATURE COLOR.
 CONTACTS: PHOSPHOR BRONZE.
 SHELL: SPCC.
 NUTS AND SHELL TAILS: BRASS.



2. FINISH:

CONTACTS: 0.76 μ m [30 μ "] GOLD PLATED ON CONTACT AREA.
 2.54 μ m [100 μ "] MIN. BRIGHT-TIN PLATED ON
 SOLDER TAIL, WITH ENTIRE CONTACT UNDERPLATED
 1.27 μ m [50 μ "] MIN. NICKEL.




SHELL: 1.27 μ m [50 μ "] MIN. NICKEL PLATED.

SHELL TAILS: 2.54 μ m [100 μ "] MIN. BRIGHT-TIN PLATED OVER
 1.27 μ m [50 μ "] MIN. NICKEL UNDERPLATED OVER.

NUTS: 1.27 μ m [50 μ "] NICKEL PLATED.

3. PIN-IN-PASTE CAPABLE TO 260°C IN ACCORDANCE WITH
TEST SPECIFICATIONS 109-201 AND 109-202.

RECOMMENDED PANEL CUTOUT



RECOMMENDED PCB LAYOUT

TOP VIEW, TOLERANCE: ±0.05

THICKNESS: 1.6mm

2041273-1

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN J. LAI 02AUG2010

CHK S. CHIEN 02AUG2010

APVD W. KODAMA 02AUG2010

PRODUCT SPEC

108-1941


APPLICATION SPEC

WEIGHT 10 GRAMS

CUSTOMER DRAWING

DIMENSIONS:

MM



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±

1 PLC ±0.3

2 PLC ±0.2

3 PLC ±0.15

4 PLC ±

ANGLES ±3°

MATERIAL SEE NOTE

FINISH SEE NOTE

TE

TE Connectivity

NAME

DVI-I ANALOG&DIGITAL CONNECTOR,
RCPT. RIGHT-ANGLE, W/O SCREW

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=2041273

SCALE

SHEET

1 OF 4

REV

A2

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION



COPYRIGHT

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1.

PARTITION

7 TRAY PER CARTON

TAPE


G.P.PASS

LABLE

1. MATERIAL:
TRAY: PVC
BOX: CORRUGATED FIBER.
2. DIMENSION:
TRAY: SEE PAGE3,4
BOX: L=326mm, W=245mm, H=140mm

5.20 Kg	3.55 Kg	60	7	420
GROSS WEIGHT	NET WEIGHT	PCS/TRAY	TRAYS/BOX	QUANTITY

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
MM

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± -
1 PLC	± -
2 PLC	± -
3 PLC	± -
4 PLC	± -
ANGLES	± -

MATERIAL

SEE NOTE

FINISH

SEE NOTE

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING



TE Connectivity

NAME

DVI-I ANALOG&DIGITAL CONNECTOR,
RCPT. RIGHT-ANGLE, W/O SCREW

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=2041273

-

SCALE

—

SHEET

2 OF 4

REV A2

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

DW

P

LTR

DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1.

—

—

—

D

D

C

C


B


B

A

A

TOP TRAY



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN —		TE Connectivity	
DIMENSIONS: MM		CHK —		NAME	
		APVD —		DVI-I ANALOG&DIGITAL CONNECTOR, RCPT. RIGHT-ANGLE, W/O SCREW	
		PRODUCT SPEC		SIZE	
		APPLICATION SPEC		CAGE CODE	
		WEIGHT		DRAWING NO	
MATERIAL SEE NOTE	FINISH SEE NOTE	CUSTOMER DRAWING		A3 00779 C=2041273	
		SCALE —		SHEET 3 OF 4	
				REV A2	

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION



COPYRIGHT

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1.

—

—

—

7.30

18.60 $\frac{0.00}{-0.30}$

SEC A-A

24.80

43.00

238.60

224.60

306.00

320.0

15.40

38.00 $\frac{0.00}{-0.30}$

SEC B-B

BOTTOM TRAY

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

CHK

APVD

PRODUCT SPEC


APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

DIMENSIONS:

MM



MATERIAL

SEE NOTE

TOLERANCES UNLESS
OTHERWISE SPECIFIED:0 PLC ± —
1 PLC ± 0.3
2 PLC ± 0.3
3 PLC ± —
4 PLC ± —
ANGLES ± 3°

FINISH

SEE NOTE



TE Connectivity

NAME

DVI-I ANALOG&DIGITAL CONNECTOR,
RCPT. RIGHT-ANGLE, W/O SCREW

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=2041273

—

SCALE —

SHEET

4 OF 4

REV A2