


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REVISED PER ECO-19-009164	23JUN2020	SJ	DR



1. WIRE RANGE: 22-16 AWG. STANDARD WIRE CROSS SECTIONAL AREA RANGE: 509-3260 CIRCULAR MILS, STRANDED
2. TERMINAL BODY MATERIAL THK IS 0.787±0.005[.031±.002]
3. RECOMMENDED OPERATING TEMP -55°C(-67°F) TO +200°C(392°F) FOR HEAT SHRINK TUBING.
4. HEAT SHRINK TUBING SHELF LIFE OF 18 MONTHS FROM DATE CODE ON LABEL.
5. TERMINAL BODY PRODUCT SPECIFICATION 108-32046. APPLICATION SPECIFICATION 114-2162.

1	1-1193336-2	HIGH AND LOW TEMPERATURE CROSS LINKED FLUOROPOLYMER HEAT SHRINK TUBING 4.78 [.187] MIN ID X 19.05±0.38 [.750±.015], RT-555-3/16-0-0.75
1	696949-1	TERMINAL BODY: COPPER PER ASTM B152 ANNEALED FINISH: NICKEL PLATE 0.00762 [.000300] MIN EXT THK PER SAE AMS QQ-N-290
-1	PART NO	DESCRIPTION

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 27JUL07	TE Connectivity							
		CHK MJ SPICER 27JUL07								
DIMENSIONS: MM [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD MJ SPICER 27JUL07	NAME HEAT RESISTANT TERMINAL KIT WIRE SIZE: 22-16 AWG -							
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.127 [.005] 4 PLC ± - ANGLES ± 1°	PRODUCT SPEC 5								
	MATERIAL SEE TABLE	FINISH SEE TABLE	APPLICATION SPEC 5	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO			
WEIGHT -			A3	00779	C-1958124	-				
CUSTOMER DRAWING					SCALE	1:1	SHEET	1 OF 1	REV	B