

THIS DRAWING IS UNPUBLISHED.
DIFFUSION RESTREINTE

© COPYRIGHT 2011

RELEASED FOR PUBLICATION
LIBRE A LA DIFFUSION

ALL RIGHTS RESERVED
TOUS DROITS RESERVES

2011

LOC

DIST

F00

REVISIONS

P	LTR	DESCRIPTION MODIFICATIONS	DATE	DWN DESS.	APVD APP.
A		FIRST ISSUE	13SEP2007	PF s	JD r
B		ADD NG9K SEALS, HEAD FORMS SET UP.	19SEP2008	PF s	JD r
C		SET UP DIM 31, 33, 34 AND 35.	17JUN2011	PF s	JD r

10.9

3

11

10

12

3.2

1.9

13

IDENTIFICATION DE LA GAMME "A" = DE 2.5 A 4 MM2

WIRE SIZE IDENTIFICATION "A" = FROM 2.5 TO 4 MM2

COUPE C-C
SECTION C-C

1

REGLAGE EN FONCTION DES FI SUR CALIBRE

GAP DEPENDENT MATING FORCE ON GAUGE

COUPE D-D
SECTION D-D

0.2 A

5.4±0.2

41

40

1.05

20

0.2 B

COUPE E-E
SECTION E-E

3.7

4.09

0.2 A

51

50

52

R2.5

Y = IDENTIFICATION MATIERE
EN Cu MICRO ALLIE VOIR TABLEAU

Y = MATERIAL IN Cu MICRO ALLOY
SEE DESCRIPTION IN TABLE

LARGEUR ENTREFER REGLER POUR
DES LANGUETTES DE 1mm

WIDTH GAP FOR 1mm TAB

ECHELLE 1:1
SCALE 1:1

1

2

3

PAS = 22

PITCH = 22

60

31

34

33

30

10.9

3.5±0.15

32

7.8±0.15

4.6

5.25±0.2

2.2

2.25

35

36.45±0.25 EN BANDE

36.45±0.25 IN STRIP

(30±0.2 APRES SEPARATION)

(30±0.2 AFTER CUTTING)

PRODUIT ASSOCIE / APPLIED PRODUCT

DESIGNATION DES JOINTS SEALS DESCRIPTION	REFERENCE PN TE	REFERENCE / PN CUSTOMER	COULEUR COLOR
JOINT UNIFILAIRE 3 A 6 MM2 SINGLE WIRE SEAL 3 TO 6 MM2	1544316-1		VERT / GREEN
SUPER JOINT UNIFILAIRE 3 A 6 MM2 SUPER SINGLE WIRE SEAL 3 TO 6 MM2	1544664-1		VERT / GREEN
JOINT UNIFILAIRE NG9K 2.5 A 5 MM2 NG9K SINGLE WIRE SEAL 2.5 TO 5 MM2	1544970-1		MARRON / BROWN

INTERFACE MONTABILITE / INTERFACE CAVITY

1544953

NOTA

1	(X) = POUR INFORMATION
2	CONDITIONNEMENT : VOIR SPECIFICATION 107-15602

NOTES

1	(X) = FOR INFORMATION
2	PACKAGING : SEE SPECIFICATION 107-15602

REFERENCE
PN TE

REFERENCE CLIENT
CUSTOMER PN

Y :
REPERE MATIERE
MATERIAL REPERE

MATIERE
MATERIAL

TRAITEMENT DE SURFACE
HEAT TREATMENT

1544964-1

S

CuNiSi SELON
SPECIFICATION: 100-1230
CuNiSi ACCORDING TO
SPECIFICATION: 100-1230

PRE-ETAME SnAg DE 1 A 3µ
SELON SPECIFICATION 112-73-2
PRE-TINNED SnAg FROM 1 TO 3µ
ACCORDING SPECIFICATION 112-73-2

1544964-2

T

PRE-ARGENTE Ag DE 1 A 3µ
SELON SPECIFICATIONS
212-7, 112-32 ET 118-91
PRE-SILVERED Ag FROM 1 TO 3µ
ACCORDING SPECIFICATIONS
212-7, 112-32 AND 118-91

THIS DRAWING IS A CONTROLLED DOCUMENT.
CE PLAN EST UN DOCUMENT CONTRÔLÉ PAR AJP INCORPORATED.
IL EST SUSCEPTIBLE D'ÊTRE MODIFIÉ. CONTACTER LE SERVICE
TECHNIQUE D'APPUI DE FRANCE POUR OBTENIR LA DERNIÈRE RÉVISION.

DIMENSIONS:

mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
TOLERANCES NON SPECIFIÉES
(SUIVANT NO DE DÉCIMALES)

1. PLC/DEC: ±

2. PLC/DEC: ±0.1

3. PLC/DEC: ±

ANGLES

FINISH

FINITION

MATERIAL
MATIERE

SEE TABLE

DWN/DESSINE
P. FLORES 13SEP07

CHK/VERIFIE
F. SAPET 13SEP07

APVD/APPROUVE
J. DAHER 13SEP07

PRODUCT SPEC
SPEC. PRODUIT
108-15382

APPLICATION SPEC
SPEC. APPLICATION
114-15105

WEIGHT
MASSE APPROX.
0.0023kg

CUSTOMER DRAWING /PLAN CLIENT

NAME
TITRE

8mm NG1+ FEMALE TERMINAL
WIRE SIZE 2.5-4 SQUARE MM

SIZE
FORMAT
A2

CAGE CODE
00779

DRAWING NO
No PLAN
C=1544964

RESTRICTED TO
RESERVE A
-

UNIQUEMENT
POUR REFERENCE

SCALE
ECHELLE 5:2

SHEET
FEUILLE 1

OF
DE 1

REV
C

1471-9 (3/11)