




REV. 0

DCO 141423

COIL: @ 25°C
 RESISTANCE _____ 500 OHMS $\pm 10\%$
 NOMINAL VOLTAGE _____ 12.0 VDC
 MUST OPERATE _____ 7.0 VDC


 MUST RELEASE _____ 4.0 VDC MAX, 0.63 VDC MIN.

ENVIRONMENT:

VIBRATION _____ 10 _____ CPS TO _____ 3000 _____ CPS @ _____ 30 _____ g's
 SHOCK _____ 75 _____ g's _____ 6 _____ MS. DURATION
 TEMPERATURE _____ -65 _____ °C TO _____ +125 _____ °C

NOTES: _____ OPERATE TIME 2.0 MS MAX.
 _____ RELEASE TIME 2.0 MS MAX.
 _____ CONTACT BOUNCE 1.5 MS MAX.

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO 1A
28 VDC RESISTIVE 100,000 OPERATIONS

DR. B.D. 10/6/99

10/6/99



COMMUNICATIONS
 INSTRUMENTS, INC.

CUST. _____ QPL
 CUST. NO. M39016/7-019L REV. _____

"J1MA" RELAY

J1MAW-12XL