






TABLE 1

SUB ASSEMBLY PART NO. AND CH. CODE	NO.	PART NO. AND CH. CODE	MATERIAL	COLOR	△ QTY.
7283-1025 ETC.	①	SEE TABLE 2	△ HPA	SEE TABLE 2	1
	②	7157-4085 △ (7B57-4085)	△ HPA	△ NATURAL	1

△ TABLE 2

SUB ASSEMBLY PART NO. AND CH. CODE	PART NO. AND CH. CODE	COLOR
7283-1025. △ △ (7C83-1025)	7183-1025 △ (7B83-1025)	NATURAL
7283-1025-10. △	7183-1025-10	DARK GRAY
7283-1025-30. △	7183-1025-30	BLACK
7283-1025-40. △	7183-1025-40	LIGHT GRAY
7283-1025-90. △	7183-1025-90	BLUE

注 記

1. 嵌合相手品番 : 7282-1025 ETC.

2. 適用端子品番 : 7116-4030 ETC.

△ 3. () 内品番はA/B回路及び特別管理回路に使用すること。

NOTES

1. MATING PART NO. : 7282-1025 ETC.

2. APPLICABLE TERMINAL NO. : 7116-4030 ETC.

△ 3. PART NUMBERS IN PARENTHESIS SHALL BE USED FOR AIR BAG (A/B)
CIRCUITS AND OTHER CIRCUITS DESIGNATED FOR SPECIAL MONITOR.

△	99.02.03	ELIMINATED COLOR NO. & ADDED A/B PART NO.. NOTE	C99-L180	T. M			
△	97.07.29	CHANGED FORM, MATERIAL & ADDED PART NO.. [A]	C97-M541	M. T			
△	90.11.10	CHANGED SPACER COLOR	C90-M204	M. H			
	90.06.07	NEW	C90-L453	S. I			
LET	DATE	REVISION RECORD	NO.	CHKD			
GENERAL TOLERANCE							
	10MAX	50MAX	100MAX	250MAX	2500VR	ANGLE	ECCENT
A	±0.15	±0.2	±0.3	±0.5	±0.75	±30'	0.1
B	±0.2	±0.3	±0.55	±0.95	±1.4	±30'	0.1
©	±0.3	±0.5	±0.8	±1.4	±2	±30'	0.15
SPECIFIED						MASS	
						g	

CUSTOMER		MATT. SPEC.		TREAT. & FIN.	
CUSTOMER PART NO.		SEE TABLE 1			
CUSTOMER DWG NO.					
OFFICE		NAME		187 2P CONNECTOR	
VENDOR		TRIAL PART NO.		SUB ASSEMBLY FEMALE	
VENDOR NO.					
DWG TYPE	DWG SOURCE	DWG DATE	UNIT	SCL	ANGLE
R	NEW	90.06.07	mm	2/1	3
APPROVED	CHECKED	CHECKED	DESIGN	DRAWN	PART NO.
山梨	山梨	山梨	Y. OHTA	杉山	CH. CODE
99.02.10	99.02.09	99.02.08	89.02.28	99.02.03	7283-1025 ETC.
YAZAKI CORPORATION					DWG NO.
					7283-1025:R
					SET DWG NO.