


D

C

B


A



NOTES:

- 1 .000030 GOLD ON CONTACT AREA, GOLD FLASH ON SOLDER AREA, ALL OVER .000050 NICKEL
- 2 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

2	1,3,6,8,9	1,3,6,7,14	2.79	[.110]	55.47	[2.184]	53.34	[2.100]	21	44	4=86479=9	
	1,3,6,8,9	15,18,20,21										
OBSOLETE	1,9,15	3,11,17	2.79	[.110]	93.57	[3.684]	91.44	[3.600]	36	74	4-86479-6	
OBSOLETE	22,24,29,35											
	3	4	2.79	[.110]	24.99	[.984]	22.86	[.900]	9	20	4-86479-5	
	NONE	NONE	2.79	[.110]	101.19	[3.984]	99.06	[3.900]	39	80	4-86479-4	
	NONE	NONE	2.79	[.110]	98.65	[3.884]	96.52	[3.800]	38	78	4-86479-3	
	NONE	NONE	2.79	[.110]	96.11	[3.784]	93.98	[3.700]	37	76	4-86479-2	
	NONE	NONE	2.79	[.110]	93.57	[3.684]	91.44	[3.600]	36	74	4-86479-1	
	NONE	NONE	2.79	[.110]	91.03	[3.584]	88.90	[3.500]	35	72	4-86479-0	
	NONE	NONE	2.79	[.110]	88.49	[3.484]	86.36	[3.400]	34	70	3-86479-9	
	NONE	NONE	2.79	[.110]	85.95	[3.384]	83.82	[3.300]	33	68	3-86479-8	
	NONE	NONE	2.79	[.110]	83.41	[3.284]	81.28	[3.200]	32	66	3-86479-7	
	NONE	NONE	2.79	[.110]	80.87	[3.184]	78.74	[3.100]	31	64	3-86479-6	
	NONE	NONE	2.79	[.110]	78.33	[3.084]	76.20	[3.000]	30	62	3-86479-5	
	NONE	NONE	2.79	[.110]	75.79	[2.984]	73.66	[2.900]	29	60	3-86479-4	
	NONE	NONE	2.79	[.110]	73.25	[2.884]	71.12	[2.800]	28	58	3-86479-3	
	NONE	NONE	2.79	[.110]	70.71	[2.784]	68.58	[2.700]	27	56	3-86479-2	
	NONE	NONE	2.79	[.110]	68.17	[2.684]	66.04	[2.600]	26	54	3-86479-1	
	NONE	NONE	2.79	[.110]	65.63	[2.584]	63.50	[2.500]	25	52	3-86479-0	
	NONE	NONE	2.79	[.110]	63.09	[2.484]	60.96	[2.400]	24	50	2-86479-9	
	NONE	NONE	2.79	[.110]	60.55	[2.384]	58.42	[2.300]	23	48	2-86479-8	
	NONE	NONE	2.79	[.110]	58.01	[2.284]	55.88	[2.200]	22	46	2-86479-7	
	NONE	NONE	2.79	[.110]	55.47	[2.184]	53.34	[2.100]	21	44	2-86479-6	
	NONE	NONE	2.79	[.110]	52.93	[2.084]	50.80	[2.000]	20	42	2-86479-5	
	NONE	NONE	2.79	[.110]	50.39	[1.984]	48.26	[1.900]	19	40	2-86479-4	
	NONE	NONE	2.79	[.110]	47.85	[1.884]	45.72	[1.800]	18	38	2-86479-3	
	NONE	NONE	2.79	[.110]	45.31	[1.784]	43.18	[1.700]	17	36	2-86479-2	
	NONE	NONE	2.79	[.110]	42.77	[1.684]	40.64	[1.600]	16	34	2-86479-1	
	NONE	NONE	2.79	[.110]	40.23	[1.584]	38.10	[1.500]	15	32	2-86479-0	
	NONE	NONE	2.79	[.110]	37.69	[1.484]	35.56	[1.400]	14	30	1-86479-9	
	NONE	NONE	2.79	[.110]	35.15	[1.384]	33.02	[1.300]	13	28	1-86479-8	
	NONE	NONE	2.79	[.110]	27.53	[1.084]	25.40	[1.000]	10	22	1-86479-7	
	NONE	NONE	2.79	[.110]	9.75	[.384]	7.62	[.300]	3	8	1-86479-6	
	NONE	NONE	2.79	[.110]	7.21	[.284]	5.08	[.200]	2	6	1-86479-5	
	NONE	NONE	2.79	[.110]	4.67	[.184]	2.54	[.100]	1	4	1-86479-4	
	NONE	NONE	2.79	[.110]	2.13	[.084]	-	-	-	2	1-86479-3	
OBSOLETE	NONE	NONE	2.79	[.110]	-	-	-	-	-	-	1-86479-2	
OBSOLETE	NONE	6	2.79	[.110]	24.99	[.984]	22.86	[.900]	9	19	1-86479-1	
-87230-2	NONE	NONE	2.79	[.110]	32.61	[1.284]	30.48	[1.200]	12	26	1-86479-0	
	NONE	NONE	2.79	[.110]	-	-	-	-	-	-	86479-9	
-87230-1	NONE	NONE	2.79	[.110]	-	-	-	-	-	-	86479-8	
	NONE	NONE	2.79	[.110]	30.07	[1.184]	27.94	[1.100]	11	24	86479-7	
	NONE	NONE	2.79	[.110]	22.45	[.884]	20.32	[.800]	8	18	86479-6	
	NONE	NONE	2.79	[.110]	17.37	[.684]	15.24	[.600]	6	14	86479-5	
	NONE	NONE	2.79	[.110]	14.83	[.584]	12.70	[.500]	5	12	86479-4	
	NONE	NONE	2.79	[.110]	12.29	[.484]	10.16	[.400]	4	10	86479-3	
	NONE	NONE	2.79	[.110]	19.91	[.784]	17.78	[.700]	7	16	86479-2	
	NONE	NONE	2.79	[.110]	24.99	[.984]	22.86	[.900]	9	20	86479-1	
	ROW E	ROW D	Z		C		B		A		NO OF POSN	PART NUMBER
	POSTS OMITTED											



RECOMMENDED BOARD LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PL	± .
1 PL	± .
2 PL	± .13 [.005]
3 PL	± .
4 PL	± .
ANGLES	± .

MATERIAL: HSG-FLAME RETARDANT THERMOPLASTIC COLOR-BLACK POSTS-PA66 BRONZE

FINISH: 1

DWN: J. KNAUB 16MAY94

CHK: J. KNITTLE 17MAY94

APVD: J. KNITTLE 17MAY94

PRODUCT SPEC: -

APPLICATION SPEC: -

WEIGHT: -

CUSTOMER DRAWING

NAME: ASSEMBLY, MOD II, DOUBLE ROW .100 X .100 CL, RIGHT ANGLE WITH SPANKED TAILS

SIZE: A1

CAGE CODE: 00779

DRAWING NO: 86479

RESTRICTED TO: -

SCALE: 4:1

SHEET: 1

OF: 1

REV: T

TE Connectivity

ASSEMBLY, MOD II, DOUBLE ROW .100 X .100 CL, RIGHT ANGLE WITH SPANKED TAILS