


**SC 3.81/03/270F 3.2SN BK BX****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

The SC pin header in 270°-outlet direction: the 270° angle exists between the plugging direction and the solder pin. The plugging direction is then parallel to the PCB. Sockets blocks, however, have an overhead plugging angle.

- More freedom when designing components and devices.
- A high component density when multiple PCBs are arranged in parallel within one housing
- The housing design is application-friendly because of the additional optional wire outlet direction.
- Available in closed (G) and screw flange (F) versions.

Weidmüller's 3.81-mm-pitch (0.15 inch) plug-in connectors are compatible with the layouts of standard connectors and offer space for labelling and coding.

**General ordering data**

|              |                                                                                                                                                         |
|--------------|---------------------------------------------------------------------------------------------------------------------------------------------------------|
| Version      | PCB plug-in connector, male header, Flange, THT solder connection, 3.81 mm, Number of poles: 3, 270°, Solder pin length (l): 3.2 mm, tinned, black, Box |
| Order No.    | <a href="#">1038420000</a>                                                                                                                              |
| Type         | SC 3.81/03/270F 3.2SN BK BX                                                                                                                             |
| GTIN (EAN)   | 4032248767199                                                                                                                                           |
| Qty.         | 50 pc(s).                                                                                                                                               |
| Product data | IEC: 320 V / 17.5 A<br>UL: 300 V / 10 A                                                                                                                 |
| Packaging    | Box                                                                                                                                                     |

## SC 3.81/03/270F 3.2SN BK BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|                          |            |                 |            |
|--------------------------|------------|-----------------|------------|
| Depth                    | 9.2 mm     | Depth (inches)  | 0.362 inch |
| Height                   | 10.3 mm    | Height (inches) | 0.406 inch |
| Height of lowest version | 7.1 mm     | Width           | 22.02 mm   |
| Width (inches)           | 0.867 inch | Net weight      | 1.825 g    |

## Environmental Product Compliance

|            |                |      |                                      |
|------------|----------------|------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1 | SCIP | 308576ca-4abc-409a-b0d0-6626109a7446 |
|------------|----------------|------|--------------------------------------|

## System specifications

|                                              |                                     |                     |                                                    |
|----------------------------------------------|-------------------------------------|---------------------|----------------------------------------------------|
| Product family                               | OMNIMATE Signal - series BC/SC 3.81 |                     |                                                    |
| Type of connection                           | Board connection                    |                     |                                                    |
| Mounting onto the PCB                        | THT solder connection               |                     |                                                    |
| Pitch in mm (P)                              | 3.81 mm                             |                     |                                                    |
| Pitch in inches (P)                          | 0.15 inch                           |                     |                                                    |
| Outgoing elbow                               | 270°                                |                     |                                                    |
| Number of poles                              | 3                                   |                     |                                                    |
| Number of solder pins per pole               | 1                                   |                     |                                                    |
| Solder pin length (l)                        | 3.2 mm                              |                     |                                                    |
| Solder pin length tolerance                  | 0 / -0.2 mm                         |                     |                                                    |
| Solder pin dimensions                        | d = 1.0 mm, Octagonal               |                     |                                                    |
| Solder pin dimensions = d tolerance          | 0 / -0.03 mm                        |                     |                                                    |
| Solder eyelet hole diameter (D)              | 1.2 mm                              |                     |                                                    |
| Solder eyelet hole diameter tolerance (D)    | + 0.1 mm                            |                     |                                                    |
| L1 in mm                                     | 7.62 mm                             |                     |                                                    |
| L1 in inches                                 | 0.3 inch                            |                     |                                                    |
| Number of rows                               | 1                                   |                     |                                                    |
| Pin series quantity                          | 1                                   |                     |                                                    |
| Touch-safe protection acc. to DIN VDE 57 106 | Safe from finger touch              |                     |                                                    |
| Touch-safe protection acc. to DIN VDE 0470   | IP 20                               |                     |                                                    |
| Volume resistance                            | ≤5 mΩ                               |                     |                                                    |
| Can be coded                                 | Yes                                 |                     |                                                    |
| Plugging force/pole, max.                    | 7 N                                 |                     |                                                    |
| Pulling force/pole, max.                     | 5 N                                 |                     |                                                    |
| Tightening torque                            | Torque type                         | Mounting screw, PCB |                                                    |
|                                              | Usage information                   | Tightening torque   | min. 0.1 Nm<br>max. 0.15 Nm                        |
|                                              |                                     | Recommended screw   | Part number <a href="#">PTSC KA 2.2X4.5 WN1412</a> |

## Material data

|                                       |              |                                       |        |
|---------------------------------------|--------------|---------------------------------------|--------|
| Insulating material                   | PA GF        | Colour                                | black  |
| Colour chart (similar)                | RAL 9011     | Insulating material group             | II     |
| Comparative Tracking Index (CTI)      | ≥ 550        | UL 94 flammability rating             | V-0    |
| Contact material                      | Copper alloy | Contact surface                       | tinned |
| Storage temperature, min.             | -40 °C       | Storage temperature, max.             | 70 °C  |
| Operating temperature, min.           | -50 °C       | Operating temperature, max.           | 120 °C |
| Temperature range, installation, min. | -25 °C       | Temperature range, installation, max. | 120 °C |

## SC 3.81/03/270F 3.2SN BK BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Rated data acc. to IEC

|                                                                           |                        |                                                                       |                  |
|---------------------------------------------------------------------------|------------------------|-----------------------------------------------------------------------|------------------|
| tested acc. to standard                                                   | IEC 60664-1, IEC 61984 | Rated current, min. number of poles (Tu=20°C)                         | 17.5 A           |
| Rated current, max. number of poles (Tu=20°C)                             | 17 A                   | Rated current, min. number of poles (Tu=40°C)                         | 17.5 A           |
| Rated current, max. number of poles (Tu=40°C)                             | 15.1 A                 | Rated voltage for surge voltage class / pollution degree II/2         | 320 V            |
| Rated voltage for surge voltage class / pollution degree III/2            | 160 V                  | Rated voltage for surge voltage class / pollution degree III/3        | 160 V            |
| Rated impulse voltage for surge voltage class/ pollution degree II/2      | 2.5 kV                 | Rated impulse voltage for surge voltage class/ pollution degree III/2 | 2.5 kV           |
| Rated impulse voltage for surge voltage class/ contamination degree III/3 | 2.5 kV                 | Short-time withstand current resistance                               | 3 x 1s with 76 A |

## Rated data acc. to CSA

|                                   |       |                                   |     |
|-----------------------------------|-------|-----------------------------------|-----|
| Rated voltage (Use group B / CSA) | 300 V | Rated current (Use group B / CSA) | 8 A |
|-----------------------------------|-------|-----------------------------------|-----|

## Packing

|           |       |            |       |
|-----------|-------|------------|-------|
| Packaging | Box   | VPE length | 75 mm |
| VPE width | 66 mm | VPE height | 37 mm |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002637    | ETIM 7.0    | EC002637    |
| ETIM 8.0    | EC002637    | ECLASS 9.0  | 27-44-04-02 |
| ECLASS 9.1  | 27-44-04-02 | ECLASS 10.0 | 27-44-04-02 |
| ECLASS 11.0 | 27-46-02-01 | ECLASS 12.0 | 27-46-02-01 |

## Important note

|                |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |
|----------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| IPC conformity | Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.                                                                                                                                                                           |
| Notes          | <ul style="list-style-type: none"> <li>Additional variants on request</li> <li>Rated current related to rated cross-section &amp; min. No. of poles.</li> <li>Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.</li> <li>P on drawing = pitch</li> <li>Long term storage of the product with average temperature of 50 °C and average humidity 70%, 36 months</li> </ul> |

## Approvals

Approvals



|                         |            |
|-------------------------|------------|
| ROHS                    | Conform    |
| UL File Number Search   | UL Website |
| Certificate No. (cURus) | E60693     |

## SC 3.81/03/270F 3.2SN BK BX

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

# Technical data

## Downloads

|                                             |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |
|---------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Approval/Certificate/Document of Conformity | <a href="#">Declaration of the Manufacturer</a>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |
| Engineering Data                            | <a href="#">CAD data – STEP</a>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |
| Engineering Data                            | <a href="#">EPLAN, WSCAD</a>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |
| Catalogues                                  | <a href="#">Catalogues in PDF-format</a>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |
| Brochures                                   | <a href="#">FL DRIVES EN</a><br><a href="#">MB DEVICE MANUF. EN</a><br><a href="#">FL DRIVES DE</a><br><a href="#">FL BUILDING SAFETY EN</a><br><a href="#">FL APPL LED LIGHTING EN</a><br><a href="#">FL INDUSTR.CONTROLS EN</a><br><a href="#">FL MACHINE SAFETY EN</a><br><a href="#">FL HEATING ELECTR EN</a><br><a href="#">FL APPL INVERTER EN</a><br><a href="#">FL_BASE_STATION_EN</a><br><a href="#">FL ELEVATOR EN</a><br><a href="#">FL POWER SUPPLY EN</a><br><a href="#">FL 72H SAMPLE SER EN</a><br><a href="#">PO OMNIMATE EN</a><br><a href="#">PO OMNIMATE EN</a> |


## SC 3.81/03/270F 3.2SN BK BX

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany


[www.weidmueller.com](http://www.weidmueller.com)

# Drawings

## Product image








## Dimensional drawing



SC 3.81/.../270F 3.2 SN...

SC 3.81/.../270G 3.2 SN...



LAYOUT FINISHED HOLES

KUNDENZEICHNUNG  
CUSTOMER DRAWING

NOTE:

n=NO OF POLES  
P=PITCH

For the mounting of PCBs, it should be noted that the rated data stated here relates only to the PCB components alone.  
The necessary creepage and clearance paths must be observed in connection with the respective applicant in accordance to IEC 664 / VDE 0110.  
The current-carrying capacity and pitch tolerance is to be determined according to DIN IEC 326 part 3 very fine.

Weidmüller PCB components are tested to the DIN EN 61984 standard, and are valid for its field of application.  
Provided that the components are used to the intended purpose, all requirements with respect to the occurring of electrical, mechanical, thermic and corrosive stress will be satisfied.

|    |         |           |
|----|---------|-----------|
| 18 | 64.77   | 2.550     |
| 17 | 60.96   | 2.400     |
| 16 | 57.15   | 2.250     |
| 15 | 53.34   | 2.100     |
| 14 | 49.53   | 1.950     |
| 13 | 45.72   | 1.800     |
| 12 | 41.91   | 1.650     |
| 11 | 38.10   | 1.500     |
| 10 | 34.29   | 1.350     |
| 9  | 30.48   | 1.200     |
| 8  | 26.67   | 1.050     |
| 7  | 22.86   | 0.900     |
| 6  | 19.05   | 0.750     |
| 5  | 15.24   | 0.600     |
| 4  | 11.43   | 0.450     |
| 3  | 7.62    | 0.300     |
| 2  | 3.81    | 0.150     |
| N  | L1 [mm] | L1 [inch] |

|                                   |  |                                |  |                                                                        |  |
|-----------------------------------|--|--------------------------------|--|------------------------------------------------------------------------|--|
| MAX. NRN./NOS.                    |  | 70834/5<br>03.07.13 ZHANG_E 01 |  | CAT.NO.: .                                                             |  |
| MODIFICATION                      |  | DATE                           |  | NAME                                                                   |  |
| DRAWN                             |  | 08.01.2009                     |  | GE_G                                                                   |  |
| RESPONSIBLE                       |  |                                |  | XU_S                                                                   |  |
| CHECKED                           |  | 08.07.2013                     |  | ZHOU_N                                                                 |  |
| APPROVED                          |  |                                |  | XU_S                                                                   |  |
| SCALE: 5/1                        |  |                                |  |                                                                        |  |
| SUPERSEDES: .                     |  |                                |  |                                                                        |  |
| <b>Weidmüller</b>                 |  |                                |  | C 46284 03                                                             |  |
| DRAWING NO. SHEET 01 OF 04 SHEETS |  |                                |  | ISSUE NO.                                                              |  |
| SC... 3.81/.../270...             |  |                                |  | STIFTLASTE RASTER 3.81 GESCHLOSSEN<br>PIN HEADER PITCH 3.81CLOSED ENDS |  |
| PRODUCT FILE: SC 3.81             |  |                                |  | 7069                                                                   |  |

## Recommended wave soldering profiles

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

### Single Wave:



### Double Wave:



### Wave soldering profiles

Wired connection elements should be processed in accordance with the DIN EN 61760-1 standard. We have included two recommendations for practical wave soldering profiles, with which Weidmüller PCB terminals and connectors are qualified.

When choosing a suitable profile for your application, the following factors also need to be considered:

- PCB thickness
- Proportion of Cu in the layers
- Single/double-sided assembly
- Product range
- Heating and cooling rates

The single and double wave profiles each indicate the recommended operating range, including the maximum soldering temperature of 260°C. In practice, the maximum soldering temperature is quite often well below the above maximum profile.

We reserve the right to make technical changes.