




MODEL NUMBER	DESCRIPTION (BOTH SIDES)	JACK INTERFACE PER MIL-STD-348 FIG XXX-X	PLUG INTERFACE PER MIL-STD-348 FIG XXX-X
ADRMF70	3 LUG	201-2	201-1
ADRMF70TL	2 LUG	201-2	201-1
ADRMF370	THREADED	202-2	202-1
ADRMF70FL	4 LUG	201-2	201-1



ADRMF70 SHOWN

NOTES: UNLESS OTHERWISE SPECIFIED.

1. MATERIAL & FINISH:

- 1.1 BODY: NICKEL PLATED BRASS
- 1.2 INSULATOR: PTFE (TEFLON)
- 1.3 INTERMEDIATE CONTACT: GOLD PLATED COPPER ALLOY
- 1.4 DIELECTRIC: PTFE (TEFLON)
- 1.5 CENTER CONTACT: GOLD PLATED COPPER ALLOY
- 1.6 GASKET: SILICONE RUBBER

2. ELECTRICAL:

- 2.1 FREQUENCY (MAX): 500 MHZ
- 2.2 IMPEDANCE: NON-CONSTANT

This PROPRIETARY Document is property of Cinch Connectivity Solutions. It is confidential in nature, non-transferable, and issued with the clear understanding that it is not to be traced or copied without permission and is returnable upon demand. INTERPRET DRAWING IN ACCORDANCE WITH ASME Y14.5-2009.	3RD ANGLE PROJECTION		TROMPETER	
	RoHS2 ☒ 2011/65/EU		Title: TRB/TRT RIGHT ANGLE ADAPTER	
	UNLESS OTHERWISE SPECIFIED UNITS: INCH .XX ±.02 .XXX ±.010 ANGLES ±2°		Model No. ADRMFXXXX	
	Size A	DO NOT SCALE DRAWING	Date: 8/10/2015	Sheet 1 OF 1