




LOC FT	DIST 0	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			A2	REVISED PER ECO-12-007964	03MAY2012	KH	MS
			A3	NEW P/N 2-1546111-6 ADDED	17OCT2017	FP	FP

D




1546111-3 AS SHOWN

SEE DETAIL X



32.30	6	2-1546111-6
128.82	25	2-1546111-5
123.74	24	2-1546111-4
118.66	23	2-1546111-3
113.58	22	2-1546111-2
108.50	21	2-1546111-1
103.42	20	2-1546111-0
98.34	19	1-1546111-9
93.26	18	1-1546111-8
88.18	17	1-1546111-7
83.10	16	1-1546111-6
78.02	15	1-1546111-5
72.94	14	1-1546111-4
67.86	13	1-1546111-3
62.78	12	1-1546111-2
57.70	11	1-1546111-1
52.62	10	1-1546111-0
47.54	9	1546111-9
42.46	8	1546111-8
37.38	7	1546111-7
32.30	6	1546111-6
27.22	5	1546111-5
22.14	4	1546111-4
17.06	3	1546111-3
11.98	2	1546111-2
DIM L	NO OF POSN	PART NUMBER

C



- 1 MATERIALS AND FINISH:
HOUSING: PA 6-6, UL 94-V0, COLOR: GRAY.
TERMINAL: COPPER ALLOY, TIN PLATED.
2. SUITABLE FOR 1.6-2.4mm PC BOARD THICKNESS.
3. RECOGNIZED UNDER THE COMPONENT PROGRAM OF
UNDERWRITERS LABORATORIES INC. FILE N° E60677.
- 4 NOT CUMULATIVE TOLERANCE

B



RECOMMENDED PC BOARD LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN	11SEP2002	TE Connectivity &DWG_TITLE &DWG_TITLE_2 5.08mm PITCH		
DIMENSIONS:			CHK	11SEP2002			
TOLERANCES UNLESS OTHERWISE SPECIFIED:			APVD	11SEP2002			
0 PLC ±			PRODUCT SPEC				
1 PLC ±0.1			APPLICATION SPEC		SIZE	CAGE CODE	DRAWING NO
2 PLC ±0.25			WEIGHT		A2	00779	C-1546111
3 PLC ±			CUSTOMER DRAWING		SCALE 5:1		
4 PLC ±					SHEET 1 OF 1		
ANGLES ±					REV A3		
FINISH							

A