


SD



NOTES:

1. MATERIALS:


INSULATORS-TEFLON, ASTM-D-4894
 CAP-VINYL
 CENTER CONTACT } BER. COP., ASTM-B-196
 OUTER CONTACT SPRING }
 INSERT
 LOCKWASHER-PHOSPHOR BRONZE, ASTM-B-103
 ALL OTHER METAL PARTS-BRASS, ASTM-B16

2. FINISHES:

OUTER CONTACT SPRING } GOLD PLATE PER MIL-G-45204
 CENTER CONTACT }
 ALL OTHER METAL PARTS-KINGS TARNISH RESISTANT NICKEL FINISH (TR-5)

3. ELECTRICAL CHARACTERISTICS:

FREQUENCY RANGE: DC-500 MHZ
 NOMINAL IMPEDANCE: 75 OHMS
 VOLTAGE BREAKDOWN: CENTER CONDUCTOR/INNER GROUND: 1500 VRMS
 INNER GROUND/OUTER GROUND: 500 VRMS



MOUNTING HOLE

SD

REVISIONS

ISSUE	CHANGES
0	ER 35441 KH 04/20/95
1	CN 36674 C KH 11/0/95
2	CN 37274 D PG 03/12/97

7709-3

7709-3SD

SCALE 2:1

APPROX SURFACE AREA

USED ON

REF: KP-8040-007-000

ADAPTER, F-F, BKHD, TRI-LOC
 SERIAL DIGITAL

DRAWN KH	DATE 04/20/95
DESIGN DW	DATE 04/21/95
APPR.	DATE

KINGS
 ELECTRONICS CO., INC.
 TUCKAHOE, NEW YORK 10707

7709-3