






E	 Top View dimensions: .670 ±.010 (17.02 ±.25), .025 (.64), .241 (6.12), .554 ±.010 (14.07 ±.25), .440 DIA. (11.18), .375 DIA. (9.53), .220 +.003 / -.000 DIA. (5.59 +.08 / -.00), .845 (21.46) REF., .518 (13.16) REF., .150 (3.81), .030 (.76), .050 (1.27), .288 (7.32).							DIMENSIONS IN INCHES (MILLIMETERS) DO NOT SCALE DRAWING		Dwg. No. GC-536-0102																							
	D	C	B	A	 Side View dimensions: .180 DIA. (4.57), .170 (4.32), .140 +.030 / -.000 SWITCH TRAVEL (3.56 +.76 / -.00), .157 +.020 / -.010 (3.99 +.51 / -.25), .040 TYP. (1.02), .102 (2.59), .160 TYP. (4.06), .075 TYP. (1.91), .394 DIA. (10.01), 3/8 - 24 UNF, .075 TYP. (1.91), .030 (.76), .050 (1.27), .288 (7.32). (ACTUATOR MAY HAVE AN .040 MAX. (1.02) APPLICATION OF PRE-LOAD TRAVEL)							 SIDE TERMINATION LAYOUT .250 TYP. (6.35), .160 TYP. (4.06), .065 TYP. (1.65), .025 +.002 / -.001 MATERIAL (0.64 +.05 / -.03) THICKNESS																					
 Bottom View dimensions: .022 x 45° (.56) CHAMFER TYP., .170 (4.32), .160 TYP. (4.06), .032 TYP. (.81), .075 TYP. (1.91). BOTTOM VIEW							 BOTTOM TERMINATION LAYOUT .160 TYP. (4.06), .065 TYP. (1.65), .216 (5.49), .025 +.002 / -.001 MATERIAL (0.64 +.05 / -.03) THICKNESS																										
TERMINATION — Insert male tabs into switch housing using side or bottom termination option. Refer to termination option layout for dimensions."																																	
<table border="1"> <tr> <td>1</td> <td>2</td> <td>3</td> <td>4</td> <td>5</td> <td>6</td> <td>7</td> <td>8</td> <td>9</td> <td>10</td> </tr> </table>										1	2	3	4	5	6	7	8	9	10														
1	2	3	4	5	6	7	8	9	10																								
FORM-B3 REVISIONS							<table border="1"> <tr> <td colspan="2"> CW INDUSTRIES Southampton, Pa. 18966 </td> <td colspan="2"> Title: SWITCH ASSEMBLY PUSH ON-PUSH OFF S.P.D.T. W/SPECIAL BUTTON </td> </tr> <tr> <td colspan="2"> TOLERANCES UNLESS OTHERWISE SPECIFIED 2 Place Decimal ±.010 3 Place Decimal ±.005 Angles ±1° </td> <td colspan="2"> METRIC 1 Place Dec. ±.25mm 2 Place Dec. ±.13mm </td> </tr> <tr> <td colspan="2"> Made for: CW IND. </td> <td colspan="2"> Division: SWITCH </td> </tr> <tr> <td colspan="2"> Drawn by: DGW 11-17-2010 </td> <td colspan="2"> Dwg. No. GC-536-0102 </td> </tr> <tr> <td colspan="2"> Checked by: G. Guld 11-18-10 </td> <td colspan="2"> </td> </tr> <tr> <td colspan="2"> Approval: EJP 11/19/10 </td> <td colspan="2"> </td> </tr> </table>			CW INDUSTRIES Southampton, Pa. 18966		Title: SWITCH ASSEMBLY PUSH ON-PUSH OFF S.P.D.T. W/SPECIAL BUTTON		TOLERANCES UNLESS OTHERWISE SPECIFIED 2 Place Decimal ±.010 3 Place Decimal ±.005 Angles ±1°		METRIC 1 Place Dec. ±.25mm 2 Place Dec. ±.13mm		Made for: CW IND.		Division: SWITCH		Drawn by: DGW 11-17-2010		Dwg. No. GC-536-0102		Checked by: G. Guld 11-18-10				Approval: EJP 11/19/10			
CW INDUSTRIES Southampton, Pa. 18966		Title: SWITCH ASSEMBLY PUSH ON-PUSH OFF S.P.D.T. W/SPECIAL BUTTON																															
TOLERANCES UNLESS OTHERWISE SPECIFIED 2 Place Decimal ±.010 3 Place Decimal ±.005 Angles ±1°		METRIC 1 Place Dec. ±.25mm 2 Place Dec. ±.13mm																															
Made for: CW IND.		Division: SWITCH																															
Drawn by: DGW 11-17-2010		Dwg. No. GC-536-0102																															
Checked by: G. Guld 11-18-10																																	
Approval: EJP 11/19/10																																	
THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO CW INDUSTRIES INCORPORATED AND ITS AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN CW INDUSTRIES PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM CW INDUSTRIES INCORPORATED, SOUTHAMPTON, PENNSYLVANIA USA.																																	