


DK-621-0938-3S ACTIVE**Raychem**

TE Internal #: 833349-000

Data Bus Connectors, Jack, Bayonet, C Polarization (Bayonet Style),
Socket[View on TE.com >](#)

Cable Assemblies > Data Bus Components > Data Bus Connectors

Data Bus Connector Type: **Jack**Data Bus Connector Style: **Bayonet**Polarization (Bayonet Style): **C**Data Bus Connector Contact Type: **Socket**

Features

Product Type Features

Product Type	Data Bus Component
Data Bus Connector Type	Jack
Data Bus Connector Style	Bayonet

Contact Features

Data Bus Connector Contact Type	Socket
---------------------------------	--------

Termination Features

Connection Type	Solder
-----------------	--------

Mechanical Attachment

Polarization (Bayonet Style)	C
------------------------------	---

Usage Conditions

Operating Temperature (Max)	125 °C
-----------------------------	--------

Operation/Application

Space-Grade	Yes
-------------	-----

Product Compliance

[For compliance documentation, visit the product page on TE.com >](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUL 2021

(219)

Candidate List Declared Against: JAN 2021

(211)

SVHC > Threshold:

Pb (37% in Solder)

Article Safe Usage Statements:

Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 750984-004
10612-24-9

Customers Also Bought

TE Part #2176402-5
3540 560R 5%



TE Part #4-2176392-5
RQ 1206 383K 0.1% 10PPM 5K RL



TE Part #1-747947-5
KIT,RCPT,25P,HDE,SHLD ENCLSRE



TE Part #YDTS26F25-37BBV001
Straight Plug: D38999, 25-37 Insert,
Electroless Nickel Plating



TE Part #YDTS20F25-37AAV001
RECP ASSY



TE Part #1-1532174-1
M83513/04-D15N, MCKS-N1-B-
25S6Q1-72.0



TE Part #CM0967-000
D-150-0348



TE Part #5-2176074-9
CPF 0201 23K2 0.5% 50PPM 1K RL

Documents

Product Drawings

[DK-621-0938-3S](#)

English

Datasheets & Catalog Pages

[Data Bus Components Brochure](#)

English

Product Specifications

[Product Specification](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English