




PART NO. AND CH. CODE	COLOR	MATING PART NO.
7123-6347, A	NATURAL	7122-6347
7123-6347-40, A	GRAY	7122-6347-40



注 記

1. 対応相手品番 : 7122-6347, -6347-40
2. 適用端子品番 : 7116-2990-02, 7116-2991-02, 7116-2992-02,
: 7116-2927-02, 7116-2928-02, 7116-2929-02.

NOTES

1. MATING PART NO. : 7122-6347, -6347-40
2. APPLICABLE TERMINAL NO. : 7116-2990-02, -2991-02, -2992-02,
: 7116-2927-02, -2928-02, -2929-02.

10. 11. 15	CHANGED PART NAME	C10-ZB06	G. M	CUSTOMER				MATL. SPEC.	PBT	TREAT. & FIN.		
00. 12. 07	CHANGED FORM	C00-M560	H. Y	CUSTOMER PART NO.	CUSTOMER DWG. NO.			NAME M-LC TYPE HOUSING				
99. 11. 16	CHANGED FORM ETC.	C99-M694	H. Y					FEMALE 4P (W, GY)				
99. 07. 22	NEW	C99-M098	H. Y	OFFICE	TRIAL PART NO.							
LET	DATE	REVISION RECORD	NO.	CHKD								
GENERAL TOLERANCE												
10MAX	50MAX	100MAX	250MAX	500VR	ANGLE	ECCENT						
A ±0.15	±0.2	±0.3	±0.5	±0.75	±30'	0.1	DWG TYPE	DWG SOURCE	DWG DATE	UNIT	SCL	ANGLE
B ±0.2	±0.3	±0.55	±0.95	±1.4	±30'	0.1	R	NEW	99. 07. 22	mm	2/1	3
C ±0.3	±0.5	±0.8	±1.4	±2	±30'	0.15	APPROVED	CHECKED	CHECKED	DESIGN	DRAWN	PART NO.
SPECIFIED							S. MIZUSE		R. CABANGAL	YOSHIDA	G. MAGNAYON	CH. CODE
							MASS					DWG NO.
							10. 11. 15		10. 11. 15	99. 06. 16	10. 11. 15	7123-6347 ETC.
							10. 11. 15					7123-6347:R
												SET DWG NO.
YAZAKI CORPORATION												