




### Features:

- ✓ Adapter maximizes space behind equipment by allowing cable attachment at 90 degrees.
- ✓ Adapter decreases stress to cable and connector assembly when a 90 degree connection is required.
- ✓ Adapter is precision machined (not die-cast) from brass.

### Materials:

|                |                            |
|----------------|----------------------------|
| Connector Body | Nickel plated brass        |
| Center Contact | Nickel plated brass        |
| Insulator (f)  | Polystyrene                |
| Insulator (m)  | Polybutylene Terephthalate |

### Ratings:

|                        |                    |
|------------------------|--------------------|
| Impedance:             | 75 Ohms            |
| Frequency:             | 0 to 500 MHz       |
| VSWR:                  | 1.5 max            |
| Contact Resistance:    | 3 Milliohms max.   |
| Voltage                | * 500 V            |
| Insulation Resistance: | 5,000 Megohms min. |
| Insertions:            | 500                |
| Temperature:           | -40 to +65° C      |

\* *Hands free testing* in controlled voltage environment: *For CE compliance:* not intended for hand held use at voltages above 33 Vrms / 70 Vdc.

All dimensions are in inches. Tolerances (except noted): .xx =  $\pm .02$ " (.51 mm), .xxx =  $\pm .005$ " (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Sales: 800-490-2361 Fax: 888-403-3360 Technical Assistance: 800-241-2060  
For "Where to Buy" information, visit the Pomona web site at [www.pomonaelectronics.com](http://www.pomonaelectronics.com)