








- NOTES**
- 1 - CORROSION RESISTANT STEEL ENCLOSURE
 - 2 - SWITCH SEALED PER MIL-PRF-8805, SYMBOL 5
 - ③ TO ADJUST ROLLER DIRECTION, REMOVE ROLLER GUIDE LOCK RING, SCREW ROLLER GUIDE DOWN AS FAR AS POSSIBLE, THEN UNSCREW TO DESIRED DIRECTION. THEN UNSCREW TO DESIRED DIRECTION. SECURE BY REPLACING ROLLER GUIDE LOCK RING
 - ④ CIRCUIT DIAGRAM AND CATALOG LISTING ARE SHOWN ON NAMEPLATE
 - 5 - COINCIDENCE OF OPERATING AND RELEASING POINTS: .010 OF PLUNGER TRAVEL
 - ⑥ HARDWARE MAY BE PACKAGED UNASSEMBLED PER MIL-PRF-8805

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED
TOLERANCES ARE

ONE PLACE (.0) $\pm .030$

TWO PLACE (.00) $\pm .015$

THREE PLACE (.000) $\pm .005$

ANGLES	$\pm$
--------	-------

WEIGHT

CHARACTERISTICS		ELECTRICAL DATA	
OPERATING FORCE - - - - -	6-12 LB	CONTACT ARRANGEMENT	
FULL OVERTRAVEL FORCE - - - - -	30 LB MAX	(2) S P D T	
RELEASE FORCE- - - - -	4 LB MIN	LOAD	28 VDC
PRETRAVEL- - - - -	.040 MAX		SEA LEVEL
DIFFERENTIAL TRAVEL- - - - -	.020 MAX	RES	5
OVERTRAVEL- - - - -	.250 MIN	IND	3
		MOTOR	4
		LAMP	

ELECTRICAL DATA		
CONTACT ARRANGEMENT		
(2) S P D T		
LOAD	28 VDC	
	SEA LEVEL	50,000 FT
RES	5	5
IND	3	3
MOTOR	4	4
LAMP		