





PC PC MOUNT



PC HOLE PATTERN
TOLERANCES FOR ALL PCB LAYOUT
DIMENSIONS TO BE $\pm .002$

SPECIFICATIONS:

MATERIALS:

CASE & BUSHING :	LCP
BRACKET :	STEEL, TIN OVER COPPER PLATED
O-RING :	NITRILE
LEVER :	BRASS, NICKEL PLATED
SPRING :	MUSIC WIRE
RETAINING PLATE :	STEEL, NICKEL PLATED
PLUNGER :	STAINLESS STEEL
INSULATOR :	PTFE
MOVEABLE CONTACT :	BRASS OR COPPER ALLOY, GOLD OVER NICKEL PLATED
TERMINALS :	BRASS, TIN OVER NICKEL IN SOLDER AREA AND GOLD OVER Ni IN CONTACT AREA

ELECTRICAL:

CONTACT RATING :	0.4 VA @ 20 VDC OR PEAK AC
INITIAL CONTACT RESISTANCE:	20 MILLIOHMS MAX.
INSULATION RESISTANCE :	1,000 MEGOHMS AT 500 VDC MIN.
DIELECTRIC STRENGTH :	1,000 VOLTS RMS AT SEA LEVEL
LIFE EXPECTANCY :	2 POSITION: 80,000 CYCLES
	3 POSITION: 60,000 CYCLES
	MOMENTARY: 30,000 CYCLES

ENVIRONMENTAL:

OPERATING TEMPERATURE : -22°F TO +185°F (-30°C TO +85°C)
STORAGE TEMPERATURE : -67°F TO +185°F (-55°C TO +85°C)

NOTES:


1. ALL MATERIAIS & FINISHES COMPLY WITH EU
DIRECTIVE 2002/95/EC OF 27JAN2003 (ROHS)

PART NUMBERING SEQUENCE

MODEL	NO. OF POLES	CONTACT RATINGS	FUNCTION	CONTACT PLATINGS	TERMINATIONS	ACTUATOR	BUSHING (PLAIN)	TAPE & REEL PKGNG.	ROHS
TST	1	1	D ON NONE ON E ON OFF ON F ON NONE (ON) G (ON) OFF (ON) H ON OFF (ON)	G	PC PC PCV P.C. WITH BRACKET RA RIGHT ANGLE VRA VERTICAL RIGHT ANGLE	1 .206" 2 .250" 4 .400"	D	TR	04

FUNCTION CHART

THE FOLLOWING FUNCTIONS
AVAILABLE IN SINGLE POLE



NONE	INDICATES NO MECHANICAL POSITION.	☐ D	2 POSITIONS	ON	NONE	ON
		☐ E	3 POSITIONS	ON	OFF	ON
OFF	INDICATES A MECHANICAL POSITION WITH NO ELECTRICAL CONNECTION.	☐ F	2 POSITIONS	ON	NONE	(ON)
		☐ G	3 POSITIONS	(ON)	OFF	(ON)
(ON)	INDICATES MOMENTARY ACTION.	☐ H	3 POSITIONS	ON	OFF	(ON)
TERMINALS CONNECTED:				☐ 1-2	☐ -	☐ 2-3

TERMINALS CONNECTED:

$$\boxed{1-2} \quad \boxed{-} \quad \boxed{2-3}$$





THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.M.M.	7-11-90	tyco Electronics Tyco Electronics Corporation Harrisburg, Pa 17105-3608					
		CHK B.J.A.	12-20-90						
DIMENSIONS: INCHES	TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .010 4 PLC ± - ANGLES ± 3'	APVD B.J.A.	12-20-90	NAME SEALED TOGGLE SWITCH, SINGLE POLE, TST SERIES -					
		PRODUCT SPEC -							
		APPLICATION SPEC -				SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
		WEIGHT -		A2	00779	C-1825455	-		
MATERIAL -	FINISH -	CUSTOMER DRAWING		SCALE	4:1	SHEET	1 of 3	REV	A

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION




© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			—	SEE SHEET 1	—	—	—



TOLERANCES FOR ALL PCB LAYOUT
DIMENSIONS TO BE $\pm.002$

RA RIGHT ANGLE



TOLERANCES FOR ALL PCB LAYOUT
DIMENSIONS TO BE $\pm.002$

VRA VERTICAL
RIGHT ANGLE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
INCHES	
	0 PLC ± -
	1 PLC ± -
	2 PLC ± -
	3 PLC ± .010
	4 PLC ± -
	ANGLES ± 3°
MATERIAL	FINISH
-	-

DWN	C.M.M.	7-11-90
CHK	B.J.A.	12-20-90
APVD	B.J.A.	12-20-90
PRODUCT SPEC		
APPLICATION SPEC		
WEIGHT	-	
CUSTOMER DRAWING		

Tyco Electronics Corporation
Harrisburg, Pa 17105-3608

NAME	SEALED TOGGLE SWITCH, SINGLE POLE, TST SERIES		
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C=1825455	-
SCALE	4:1	SHEET	2 OF 3
REV	A		

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			—	SEE SHEET 1	—	—	—

D

C

B



A

D

C

B


A




TOLERANCES FOR ALL PCB LAYOUT
DIMENSIONS TO BE ±.002

PCV PC WITH VERTICAL
SUPPORT BRACKET

ACTUATORS



1825455

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	C.M.M.	7-11-90	tyco			Tyco Electronics Corporation			
		CHK	B.J.A.	12-20-90	Electronics			Harrisburg, Pa 17105-3608			
DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD	B.J.A.	12-20-90	NAME SEALED TOGGLE SWITCH, SINGLE POLE, TST SERIES -						
INCHES		PRODUCT SPEC									
	0 PLC	±	-	APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO			
	1 PLC	±	-								
	2 PLC	±	-								
	3 PLC	±	-								
	4 PLC	±	.010								
	ANGLES	±	3°								
MATERIAL	FINISH	WEIGHT		-	A2		00779		C=1825455		
-	-	CUSTOMER DRAWING			SCALE		4:1		SHEET 3 OF 3		
										REV A	