






- 注記
- 適用電線サイズ : GNS 0.3~0.85, AYS 0.3~0.5
 - かん合メス端子品番 : 7116-1680-02

NOTES

- APPLICABLE WIRE SIZE: GNS 0.3~0.85, AYS 0.3~0.5
- MATING FEMALE TERMINAL PART NO.: 7116-1680-02



SEC. A-A



DATE	REVISION RECORD	NO.	CHKD
2010/03/25	CORRECTION OF	C10-Z168	T.W
1990/10/24	CLERICAL ERROR ETC.	C90-7548	M.S
1990/09/25	CHANGED MATERIAL	C90-1993	S.I
	NEW		

GENERAL TOLERANCE						
	10MAX	50MAX	100MAX	250MAX	250OVR	ANGLE
A	± 0.15	± 0.2	± 0.3	± 0.5	± 0.75	$\pm 30^\circ$
B	± 0.2	± 0.3	± 0.55	± 0.95	± 1.4	$\pm 30^\circ$
C	± 0.3	± 0.5	± 0.8	± 1.4	± 2	$\pm 30^\circ$
SPECIFIED						MASS

CUSTOMER		CUSTOMER PART NO.		CUSTOMER DWG NO.		MATERIAL		TREAT.		ISSUE MARK	
OFFICE		TRIAL PART NO.				SPEC. Δ COPPER ALLOY (C=0.25)		& FIN.		TIN PLATING	
VENDOR		DWG TYPE		DWG SOURCE		DWG DATE		UNIT		SQ.	
R		NEW		1990/09/25		mm		10:1		3	
H. KONDO		K. SUZUKI		T. MATANEBE		ISHI ZUKA		M. MORAL			
2010/03/25		2010/03/25		2010/03/25		1989/04/06		2010/03/25			
PART NO.		7114-1680-02		PART NO.		7114-1680-02		PART NO.		7114-1680-02	
DWG NO.		7114-1680-02		DWG NO.		7114-1680-02		DWG NO.		7114-1680-02	
YAZAKI CORPORATION											