





PRODUCT NUMBER	PITCH
TAx21xxBBJ0G	7.50 mm



RECOMMENDED P.C.B LAYOUT
TOP VIEW

Material

- Item ① Terminal body(metal housing): Brass(CuZn), Tin plated
- Item ② Terminal screw: Steel Zinc plating "-" slot type
- Item ③ Wire guard: Stainless steel
- Item ④ Insulator (housing): Thermoplastic (UL94V-0)

Electrical UL

- Voltage rating: 250VAC
- Current rating: 16A
- Wire range:
 - Solid wire(AWG): 14-22
 - Stranded wire(AWG): 14-22
- Torque: 3.5Lb-In
- Screw: M3
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.5KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval:

N = Number of poles
Dim L=Nx7.5
Dim P=(N-1)x7.5

Poles	Dim P	Dim L
2-4p	±0.10	±0.15
5-8p	±0.20	±0.20
9-12p	±0.25	±0.30
13-16p	±0.30	±0.40

PART NO.: TA xx 21 x x BBJ0 G

End stackable		Body Color		DIM A Length		RoHS compliant (lead<4%) In copper Alloy
No. of poles						
02 2 poles	3	Red (RAL3001/D)	0	4.4mm		
03 3 poles	4	Orange(RAL2011/P)	1	3.8mm		
...	...	Yellow(RAL1018/A)	2	3.5mm		
...	...	Green(RAL6018/T)				
16 16 poles	6	Blue (RAL5015/A)				
	8	Grey(RAL7035/D)				
	9	White(RAL1102)				
	C	Green(RAL6018/U)				

mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection	product family			
ltr	ecn	no	dr	date	tolerances unless otherwise specified		TERMINAL BLOCK			
					angles	MM	title			
					tolerances		TERMINAL BLOCK			
					X±0.5		WIRE PROTECTOR, 180D WIRE INLET, ONE INTERLOCK			
					X.X±0.3		dwg no			
					X*±1°		sheet 1 of 1 size			
							TAXx21xxBBJ0G			
							A4			
							type			
							CUSTOMER Drawing			
sheet index	revision	A								
	sheet	1								