


RECOMMENDED P.C.B. LAYOUT





CIRCUIT: SPDT
CONTACT CONFIGURATION

SWITCH FUNCTION		
PDS. 1	PDS. 2	PDS. 3
ON	NONE	<ON>
2-3	NONE	2-1

() = Momentary

NOTES:


1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REF. ONLY
4. CONTACT RATING: 3A @ 120 VAC or 28 VDC, 1A @ 250 VAC
- ▲ 5. CONTACTS: SILVER
6. ELECTRIC LIFE: 30,000 make-and-break cycles at full load.
7. INSULATION RESISTANCE: 1,000 M ohm min.
8. DIELECTRIC STRENGTH: 1,000 V RMS @sea level.
9. OPERATING TEMP.: -30°C to 85°C
10. HARDWARE TO BE SHIPPED BULK
T200000-LOCK WASHER-QTY-1
T200002-LOCK RING-QTY-1
T200001-HEX NUT-QTY-2



E-SWITCH
MARKING ON
OPPOSITE SIDE

▲ NO EPOXY ON TERMINALS
BELOW THIS SURFACE

-C-



TITLE 200MSP2T1B1M2QEH

SCALE 2:1

DATE 8/4/2015

DR MW

DWG ST213005

REV A

THE INFORMATION CONTAINED IN THIS DOCUMENT
IS PROPRIETARY TO E-SWITCH AND IS
NOT TO BE COPIED OR TRANSFERRED