






PART NO.	LARGE FLANGE LED TYPE	"A" DIA.	"B"	"C"	"D" DIA.	"E"	MOUNTING HOLE DIA.	PANEL THICKNESS
LEDCR-104	T-1	.21 (5.3)	.21 (5.3)	.015 (0.38)	.24 (6.1)	.14 (3.6)	.174-.180 (4.4-4.6)	.032-.125
LEDCR-174	T-1 3/4	.30 (7.6)	.26 (6.6)	.030 (0.76)	.35 (8.9)	.16 (4.1)	.267-.273 (6.8-6.9)	(0.8-3.2)



CLIP



RING

NOTES:

1. MATERIAL:

LEDCR-104 CLIP AND RING: NYLON 6/6 (RMS-43) UL94-V0.

LEDCR-174, CLIP: NYLON 6/6 (RMS-43) UL94-V0,

RING: NYLON 6/6 (RMS-48) UL94-V2.

2. COLOR: BLACK.

2. COLOR: BLACK.			TITLE: LED HOLDER SET (CLIP AND RING)						DWG IN IN (MM)	
			TOLERANCES UNLESS NOTED .XX=±.010 .XXX=±.005 FRAC=±1/64 ANG=±1°		FILE # LEDCR MAT'L: SEE NOTES	DWN: J.B. DT: 12-12-96	APP: DT:	FINAL		
C	SEE ECN #979 FOR CHANGES	SK 04.12.05			RE: RICHCO, INC. RICHCO INC. PO BOX 804238, CHICAGO, 60680 (773) 539-4060			PART # SEE TABLE	PRINT TYPE CA	
B	COMPLETELY REDRAWN	SM 05.16.02								
A	CHANGED FILE NO.	SM 03.18.02								
REV	DESCRIPTION	ENGR DATE								