

CUSTOMER: \_\_\_\_\_

DATE: \_\_\_\_\_

## APPROVAL SPECIFICATION

**ROHS+HS**  
COMPLIANT

PRODUCT NAME: SMD power inductor

YOUR PART NO. :

OUR PART NO. : MPSM160808BE2R2M20-LF

VERSION: V1.1

RECEPTION

THE SPECIFICATION HAS BEEN ACCEPTED.

COMPANY:

DATE:

CFMD

CHKD

RCVD

MANUFACTURING NAME

SHENZHEN MICROGATE TECHNOLOGY CO., LTD  
Address: Microgate Technology Building, No. 16,  
Technology Road, Pingshan, Shenzhen, China.  
Postcode: 518118  
TEL: 86-755-28085000  
FAX: 86-755-28085605

CFMD.	CHKD.	DSGD.
Charles	Wang Yusheng	Liu Wei

## CATALOG

	<b>Component SPEC Version Record.....</b>	<b>3</b>
<b>1</b>	<b>Scope.....</b>	<b>4</b>
<b>2</b>	<b>Product Identification.....</b>	<b>4</b>
<b>3</b>	<b>Appearance and dimensions.....</b>	<b>4</b>
<b>4</b>	<b>Testing Conditions.....</b>	<b>5</b>
<b>5</b>	<b>Electrical Characteristics And Test Instruments.....</b>	<b>5</b>
<b>6</b>	<b>Condition of work.....</b>	<b>5</b>
<b>7</b>	<b>Reliability .....</b>	<b>6-8</b>
<b>8</b>	<b>Recommended Soldering Conditions.....</b>	<b>8</b>
<b>9</b>	<b>Package Information.....</b>	<b>9</b>
<b>10</b>	<b>Products Storage.....</b>	<b>10</b>

**Component SPEC Version Record**

Rev.	Effective Date	Changed Contents	Change Reasons	Approved By
1.0	2020.03.20	New released	/	Charles
1.1	2024.08.13	Update packaging quantities: from 2000PCS/Reel.to 3000PCS/Reel	/	Charles

## 1. Scope


This specification applies to the MPSM160808BE series of SMD power inductor.

## 2. Product Identification

MPSM    160808    BE    2R2    M    20 - LF  
①                      ②                      ③                      ④                      ⑤                      ⑥                      ⑦

- ① Product Symbol.
- ② Product dimensions
- ③ Special process code.
- ④ Inductance Value: ( R56:0.56 uH; 2R2: 2.2uH;)
- ⑤ Inductance Tolerance: (M:  $\pm 20\%$  ; N:  $\pm 30\%$ )
- ⑥ Process code
- ⑦ Lead free product.

## 3. Appearance and Dimensions



Note: Gray area is electrode

Dimensions in mm						
A	B	C	D	f	g	h
1.60 $\pm$ 0.20	0.80 $\pm$ 0.20	0.80Max.	0.50 Typ.	0.40 Typ.	1.70 Typ.	0.9 Typ.

## 4. Testing Conditions

Unless otherwise specified, the standard conditions for measurement/test as:

Ambient Temperature : 5 to 35℃

Relative Humidity: 25 to 85% RH

Atmospheric Pressure: 86 to 106 kPa

If any doubt on the results, measurements/tests should be made within the following limits:

Ambient Temperature : 25±1℃

Relative Humidity: 60 to 70% RH

Atmospheric Pressure: 86 to 106 kPa

## 5. Electrical Characteristics And Test Instruments

Microgate Part No.	Inductance L0 (uH) 1MHz &1V	DCR(mΩ)		Isat (A)		Irms (A)	
		Max.	Typ.	Max.	Typ.	Max.	Typ.
MPSM160808BE2R2M20-LF	2.2±20%	290	241	1.2	1.3	1.0	1.1

### Test instruments and remarks

\* L test by CHROMA 3302 meter or equivalent.

\* DCR test by Tonghui TH2516B meter or equivalent.

\* CHROMA 3302 and 1320 meter for IDC.


\* Rated current: Isat or Irms, whichever is smaller:

Isat: DC current (A) that will cause L0 to drop approximately 30%.


Irms: DC current (A) that will cause an approximate  $\Delta T$  of 40℃.

\* Maximum rated voltage: DC 20 V.

\* The part temperature (ambient + temp rise) should not exceed 125℃ under worse case operating conditions. Circuit design, component placement, PCB trace size and thickness, airflow and other cooling provision all affect the part temperature. Part temperature should be verified in the end application.



Isat test schematic diagram



Irms test schematic diagram

## 6. Condition of work

Operating temperature range: -55℃ ~ +125℃.(Including self-heating)

SHENZHEN MICROGATE TECHNOLOGY CO., LTD.

Add: Microgate Technology Building, No. 16, Technology Road, Pingshan, Shenzhen, China.





Tel: +86-755-28085000




Fax: +86-755-28085605

Postcode: 518118

5/10

## 7. Reliability

No.	Item	Requirements	Test Methods and Remarks	Reference	Sample Size
1	Solderability	Terminal area must have 95% min. solder coverage.	①8hours steam age test. ②Temperature: $245 \pm 5^{\circ}\text{C}$ , flux 5-10 s. ③Sample immersion tin furnace $5 \pm 0.5\text{s}$ . ④Immersed and in and out of speed: $25 \pm 6\text{mm/s}$ .	AEC-Q200 (J-STD-002)	15
2	Resistance to Soldering Heat		①The peak temperature: $260 \pm 5/-0^{\circ}\text{C}$ . ②Reflow: 3 times. ③Temperature curve is as below: 	AEC-Q200 (MIL-STD-202 Method 210)	30
3	High Temperature Storage		①Temperature: $125 \pm 2^{\circ}\text{C}$ . ②Time : 1000 hours. ③Measurement at $24 \pm 4$ hours after test conclusion. 	AEC-Q200 (MIL-STD-202 Method 108)	77
4	Low Temperature Storage	(1) No physical damage. (2) $ \Delta L_0/L_0  \leq 10\%$	①Temperature: $-55 \pm 2^{\circ}\text{C}$ . ②Time : 1000 hours. ③Measurement at $24 \pm 4$ hours after test conclusion. 	JESD22-A119	77
5	Thermal shock		①First $-40^{\circ}\text{C}$ for 15 minutes, last $125^{\circ}\text{C}$ 15 minutes as 1 cycle. Go through 300 cycles. ②Max transfer time is 20 second. ③Measurement at $24 \pm 4$ hours after test conclusion. 	MIL-STD-202 Method 107	30

No.	Item	Requirements	Test Methods and Remarks	Reference	Sample Size
6	Humidity Resistance	(1) No physical damage. (2) $ \Delta L_0/L_0  \leq 10\%$	①1000 hours, 85 °C/85%RH. ②Unpowered. ③Measurement at 24±4 hours after test conclusion. 	AEC-Q200 (MIL-STD-202 Method 103)	77
7	Terminal Strength	No physical damage.	①The test samples shall be soldered to the board. ②5.0N, 10±0.5s. 	MIL-STD-202	30
8	Board Flex	(1) No physical damage. (2) $ \Delta L_0/L_0  \leq 10\%$	①Part mounted on a 100mm*40mm FR4 PCB board, which is 1.6±0.2 mm thick and as a Layer-thickness 35 μm ± 10 μm. ②Bending speed is 1mm/s. ③Keeping the P.C Board 2 mm minimum for 60 seconds. 	AEC-Q200 (AEC-Q200-005)	30
9	Drop		①Height: 1 m, Free fall, 10times. ②Direction: 1 Angle, 1side, 2surface.	JESD22-B111	30
10	Vibration		①Frequency range : 10~2000Hz. ②Amplitude: 1.5mm, 5g. ③Sweep time and duration: 10~2000~10Hz for 20 minutes. ④Each four hours(12 times) in X,Y,Z direction, 12 hours in total.	AEC-Q200 (MIL-STD-202 Method 204)	30


No.	Item	Requirements	Test Methods and Remarks	Reference	Sample Size
11	Loading at High Temperature	(1) No physical damage. (2) $ \Delta L_0/L_0  \leq 10\%$	① Temperature: $85 \pm 2^\circ\text{C}$ . ② Time : 1000 hours. ③ Rated current. ④ Measurement at $24 \pm 4$ hours after test conclusion.	AEC-Q200 (MIL-PRF-27)	77

\*All above experiments items need 3 Lot., sample size is as specified in the table above.

\*Sample size standard is from AEC-Q200 : qualification sample size requirements.

## 8. Recommended Soldering Conditions

### (1) Reflow soldering conditions



\*Above reflow soldering curve is from J-STD-020D.

### (2) Iron soldering


The following conditions must be strictly followed when using a soldering iron.

Pre-heating	150°C 1 minute
Tip temperature	350°C max
Soldering iron output	30w max
End of soldering iron	$\phi$ 1mm max
Soldering time	3 seconds max




## 9. Package Information

(1) Dimension of tape (Unit: mm)




W	A0	B0	K0	E	F	P	P0	D0	T
8.0±0.1	1.15±0.05	1.95±0.05	0.98±0.1	1.75±0.1	3.5±0.1	4.0±0.1	4.0±0.1	1.5+0.1/-0.0	0.18±0.02

(2) Dimension of reel (Unit: mm)



Symbol	Dimension
A	178±2
B	58±2
C	13.5±0.2
G	9.0±0.5

(3) Taping figure and drawing direction




(4) Packaging quantities: 3000PCS/Reel.

(5) Peeling strength of cover tape:

The peel force of top cover tape shall be between 0.10N to 1.0N

\*the peel force standard is from EIA-481-D



Room Temp. (°C)	Room Humidity (%)	Room aim (hpa)	Peel Speed mm/min
5-35	45-85	860-1060	300

SHENZHEN MICROGATE TECHNOLOGY CO., LTD.

Add: Microgate Technology Building, No. 16, Technology Road, Pingshan, Shenzhen, China.

Tel: +86-755-28085000

Fax: +86-755-28085605

Postcode: 518118

9/10

## 10. Products Storage

### (1) Storage period

Products which inspected in MICROGATE over 12 months ago should be examined and used, which can be confirmed with inspection No. marked on the container. Solderability should be checked if this period is exceeded.

### (2) Storage conditions

Products should be storage in the warehouse on the following conditions:

Temperature: -10 ~+ 35℃

Humidity: Less than 70% relative and humidity

No rapid change on temperature and humidity.

- (3) Don't keep products in corrosive gases such as sulfur, chlorine gas or acid, or it may cause oxidization of electrode, resulting in poor solderability.
- (4) Products should be storage on the palette for the prevention of the influence from humidity, dust and so on.
- (5) Products should be storage in the warehouse without heat shock, vibration, direct sunlight and so on.
- (6) Products should be storage under the airtight packaged condition.