




VM8001

80V N-Channel MOSFETs

General Description

These N-Channel enhancement mode power field effect transistors are using trench DMOS technology. This advanced technology has been especially tailored to minimize on-state resistance, provide superior switching performance, and withstand high energy pulse in the avalanche and commutation mode. These devices are well suited for high efficiency fast switching applications.

PPAK5X6 Pin Configuration



BVDSS	RDS(ON)	ID
80V	3mΩ	150A

Features

- 80V,150A, $R_{DS(ON)} = 3m\Omega @ V_{GS} = 10V$
- Improved dv/dt capability
- Fast switching
- 100% EAS Guaranteed
- Green Device Available

Applications

- Networking
- Load Switch
- LED applications

Absolute Maximum Ratings $T_c=25^\circ\text{C}$ unless otherwise noted

Symbol	Parameter	Rating	Units
V_{DS}	Drain-Source Voltage	80	V
V_{GS}	Gate-Source Voltage	± 20	V
I_D	Drain Current – Continuous ($T_c=25^\circ\text{C}$)	150	A
	Drain Current – Continuous ($T_c=100^\circ\text{C}$)	96	A
I_{DM}	Drain Current – Pulsed ¹	600	A
EAS	Single Pulse Avalanche Energy ²	520	mJ
IAS	Single Pulse Avalanche Current ²	102	A
P_D	Power Dissipation ($T_c=25^\circ\text{C}$)	192	W
	Power Dissipation – Derate above 25°C	1.54	W/ $^\circ\text{C}$
T_{STG}	Storage Temperature Range	-55 to 150	$^\circ\text{C}$
T_J	Operating Junction Temperature Range	-55 to 150	$^\circ\text{C}$

Thermal Characteristics

Symbol	Parameter	Typ.	Max.	Unit
$R_{\theta JA}$	Thermal Resistance Junction to ambient	---	62	$^\circ\text{C/W}$
$R_{\theta JC}$	Thermal Resistance Junction to Case	---	0.65	$^\circ\text{C/W}$



Electrical Characteristics ($T_J=25^\circ\text{C}$, unless otherwise noted)

Off Characteristics

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
BV_{DSS}	Drain-Source Breakdown Voltage	$V_{GS}=0V$, $I_D=250\mu A$	80	---	---	V
I_{DSS}	Drain-Source Leakage Current	$V_{DS}=80V$, $V_{GS}=0V$, $T_J=25^\circ\text{C}$	---	---	1	μA
		$V_{DS}=64V$, $V_{GS}=0V$, $T_J=85^\circ\text{C}$	---	---	10	μA
I_{GSS}	Gate-Source Leakage Current	$V_{GS}=\pm 20V$, $V_{DS}=0V$	---	---	± 100	nA

On Characteristics

$R_{DS(ON)}$	Static Drain-Source On-Resistance	$V_{GS}=10V$, $I_D=20A$	---	2.5	3	$m\Omega$
$V_{GS(th)}$	Gate Threshold Voltage	$V_{GS}=V_{DS}$, $I_D=250\mu A$	2	3	4	V
g_{fs}	Forward Transconductance	$V_{DS}=10V$, $I_D=3A$	---	14	---	S

Dynamic and switching Characteristics

Q_g	Total Gate Charge ^{3, 4}	$V_{DS}=40V$, $V_{GS}=10V$, $I_D=75A$	---	68	100	nC
Q_{gs}	Gate-Source Charge ^{3, 4}		---	19	30	
Q_{gd}	Gate-Drain Charge ^{3, 4}		---	20	30	
$T_{d(on)}$	Turn-On Delay Time ^{3, 4}	$V_{DD}=40V$, $V_{GS}=10V$, $R_G=6\Omega$ $I_D=75A$	---	30	45	ns
T_r	Rise Time ^{3, 4}		---	25	40	
$T_{d(off)}$	Turn-Off Delay Time ^{3, 4}		---	45	70	
T_f	Fall Time ^{3, 4}		---	25	40	
C_{iss}	Input Capacitance	$V_{DS}=40V$, $V_{GS}=0V$, $F=1MHz$	---	4600	6900	pF
C_{oss}	Output Capacitance		---	990	1500	
C_{rss}	Reverse Transfer Capacitance		---	16	24	
R_g	Gate resistance	$V_{GS}=0V$, $V_{DS}=0V$, $F=1MHz$	---	1.8	---	Ω

Drain-Source Diode Characteristics and Maximum Ratings

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
I_S	Continuous Source Current	$V_G=V_D=0V$, Force Current	---	---	150	A
I_{SM}	Pulsed Source Current		---	---	300	A
V_{SD}	Diode Forward Voltage	$V_{GS}=0V$, $I_S=1A$, $T_J=25^\circ\text{C}$	---	---	1	V
t_{rr}	Reverse Recovery Time	$V_R=50V$, $I_S=10A$	---	70	---	ns
Q_{rr}	Reverse Recovery Charge	$di/dt=100A/\mu s$, $T_J=25^\circ\text{C}$	---	160	---	nC

Note :

1. Repetitive Rating : Pulsed width limited by maximum junction temperature.
2. $V_{DD}=50V$, $V_{GS}=10V$, $L=0.1mH$, $I_{AS}=102A$, $R_G=25\Omega$, Starting $T_J=25^\circ\text{C}$.
3. The data tested by pulsed , pulse width $\leq 300\mu s$, duty cycle $\leq 2\%$.
4. Essentially independent of operating temperature.




Fig.1 Typical Output Characteristics




Fig.2 Continuous Drain Current vs. T_C




Fig.3 Normalized R_{DS(on)} vs. T_J




Fig.4 Normalized V_{th} vs. T_J




Fig.5 Turn-On Resistance vs. V_{GS}




Fig.6 Turn-On Resistance vs. I_D




Fig.7 Capacitance Characteristics




Fig.8 Gate Charge Characteristics




Fig.9 Normalized Transient Impedance




Fig.10 Maximum Safe Operation Area




Fig.11 Switching Time Waveform





Fig.12 Gate Charge Waveform




PPAK5x6 PACKAGE INFORMATION



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	MAX	MIN	MAX	MIN
A	1.200	0.850	0.047	0.031
b	0.510	0.300	0.020	0.012
C	0.300	0.200	0.012	0.008
D1	5.400	4.800	0.212	0.189
D2	4.310	3.610	0.170	0.142
E	6.300	5.850	0.248	0.230
E1	5.960	5.450	0.235	0.215
E2	3.920	3.300	0.154	0.130
e	1.27BSC		0.05BSC	
H	0.650	0.380	0.026	0.015
K	---	1.100	---	0.043
L	0.710	0.380	0.028	0.015
L1	0.250	0.050	0.009	0.002
θ	12°	0°	12°	0°



PPAK5X6 RECOMMENDED LAND PATTERN



unit : mm

Contact Information

Viva Electronics Incorporated

10F-1, No. 32, Gaotie 2nd Rd., Zhubei City, Hsinchu County, Taiwan, R.O.C.

Tel: 886-3-6579508

Fax: 886-3-6579509

WWW: <http://www.viva-elec.com.tw>

Sales: sales@viva-elec.com.tw

FAE Support: fae@viva-elec.com.tw