

Low Pass Filter

50Ω DC to 70 MHz


Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	0.5W Max
Permanent damage may occur if any of these limits are exceeded.	

Pin Connections

RF IN	2
RF OUT	6
GROUND	1, 3, 4, 5, 7, 8

Outline Drawing







Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H	J
.350	.350	.100	.175	.075	.100	.110	.040	.080
8.89	8.89	2.54	4.45	1.91	2.54	2.79	1.02	2.03
K	L	M	N	P	Q	R		
.050	.040	.195	.390	.120	.390	.070		wt.
1.27	1.02	4.95	9.91	3.05	9.91	1.78		grams
								0.25

Note: Please refer to case style drawing for details

Demo Board MCL P/N: TB-332 Suggested PCB Layout (PL-176)



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

RLP-70+


Generic photo used for illustration purposes only
CASE STYLE: GP731

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Reel Size	Devices/Reel
7"	10, 20, 50, 100, 200
13"	500, 1000

Features

- high rejection
- sharp insertion loss roll off
- excellent VSWR, 1.1:1 typ. @ passband
- aqueous washable


Applications

- wireless communications
- receivers / transmitters


Low Pass Filter Electrical Specifications (T_{AMB} = 25°C)

PASSBAND (MHz)	f _{co} , MHz Nom.	STOPBAND (MHz)	VSWR (:1)
(Loss < 2dB)	(Loss 3dB)	(Loss > 20dB) (Loss > 40dB)	Passband Typ. Stopband Typ.
DC - 70	77	100 - 115 115 - 1000	1.1 20

Typical Frequency Response



Functional Schematic



Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB) $\bar{x}$	Insertion Loss (dB) σ	Return Loss (dB)	Frequency (MHz)	Group Delay (nSec)
0.5	0.26	0.01	29.63	2.0	8.88
30.0	0.46	0.00	26.01	4.0	8.73
50.0	0.73	0.01	34.05	10.0	8.72
70.0	1.44	0.03	26.46	16.0	8.84
74.0	1.96	0.07	16.38	20.0	8.98
77.0	2.86	0.13	10.21	26.0	9.24
80.0	4.64	0.23	5.93	30.0	9.48
84.0	8.66	0.34	2.87	36.0	9.88
86.0	11.14	0.36	2.12	40.0	10.24
92.0	19.15	0.38	1.17	46.0	10.90
100.0	29.98	0.41	0.81	50.0	11.51
110.0	44.80	0.63	0.64	56.0	12.70
115.0	54.65	1.12	0.58	60.0	13.75
200.0	75.92	2.39	0.26	66.0	16.08
400.0	76.19	1.55	0.12	70.0	18.62
600.0	84.79	4.15	0.09	76.0	24.82
800.0	78.30	3.25	0.13	77.0	25.65
1000.0	58.09	0.60	0.14	80.0	26.75