


**SV 7.62HP/04/270MF3 3.5SN BK BX****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

Similar to illustration

270° male header with middle flange with a 7.62 pitch. Meets the requirements of IEC 61800-5-1 and enables UL approval as per UL840 600 V. Without a female header, the mating profile guarantees minimum touch safety of >3 mm with 20 N pressure on the test finger. The automatically locking middle flange which can optionally also be screwed, reduces space requirements by one pitch width in comparison with conventional solutions.

On request: available with screw flange or without flange.

**General ordering data**

|              |                                                                                                                                                                             |
|--------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Version      | PCB plug-in connector, male header, closed side, Middle flange, THT solder connection, 7.62 mm, Number of poles: 4, 270°, Solder pin length (l): 3.5 mm, tinned, black, Box |
| Order No.    | <a href="#">1048550000</a>                                                                                                                                                  |
| Type         | SV 7.62HP/04/270MF3 3.5SN BK BX                                                                                                                                             |
| GTIN (EAN)   | 4032248786473                                                                                                                                                               |
| Qty.         | 48 pc(s).                                                                                                                                                                   |
| Product data | IEC: 1000 V / 57 A<br>UL: 300 V / 40.5 A                                                                                                                                    |
| Packaging    | Box                                                                                                                                                                         |

Creation date September 15, 2022 10:31:32 PM CEST

## SV 7.62HP/04/270MF3 3.5SN BK BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|                          |          |                 |            |
|--------------------------|----------|-----------------|------------|
| Depth                    | 28.3 mm  | Depth (inches)  | 1.114 inch |
| Height                   | 14.9 mm  | Height (inches) | 0.587 inch |
| Height of lowest version | 11.4 mm  | Width           | 38.1 mm    |
| Width (inches)           | 1.5 inch | Net weight      | 3 g        |

## System specifications

|                                                   |                                      |                                              |                                            |
|---------------------------------------------------|--------------------------------------|----------------------------------------------|--------------------------------------------|
| Product family                                    | OMNIMATE Power - series BV/SV 7.62HP | Type of connection                           | Board connection                           |
| Mounting onto the PCB                             | THT solder connection                | Pitch in mm (P)                              | 7.62 mm                                    |
| Pitch in inches (P)                               | 0.3 inch                             | Outgoing elbow                               | 270°                                       |
| Number of poles                                   | 4                                    | Number of solder pins per pole               | 2                                          |
| Solder pin length (l)                             | 3.5 mm                               | Solder pin length tolerance                  | +0.1 / -0.3 mm                             |
| Solder pin dimensions                             | 0.8 x 1.0 mm                         | Solder eyelet hole diameter (D)              | 1.3 mm                                     |
| Solder eyelet hole diameter tolerance (D)+ 0,1 mm |                                      | L1 in mm                                     | 30.48 mm                                   |
| L1 in inches                                      | 1.2 inch                             | Number of rows                               | 1                                          |
| Pin series quantity                               | 1                                    | Touch-safe protection acc. to DIN VDE 57 106 | Touch-safe above the printed circuit board |
| Touch-safe protection acc. to DIN VDE 0470        | IP 20                                | Protection degree                            | IP20, when fully mounted                   |
| Volume resistance                                 | 2.00 mΩ                              | Can be coded                                 | Yes                                        |
| Plugging cycles                                   | 25                                   |                                              |                                            |

## Material data

|                                       |                                |                                       |        |
|---------------------------------------|--------------------------------|---------------------------------------|--------|
| Insulating material                   | PA GF                          | Colour                                | black  |
| Colour chart (similar)                | RAL 9011                       | Insulating material group             | II     |
| Comparative Tracking Index (CTI)      | ≥ 500                          | UL 94 flammability rating             | V-0    |
| Contact material                      | Copper alloy                   | Contact surface                       | tinned |
| Layer structure of solder connection  | 1...3 µm Ni / 4...6 µm Sn matt | Storage temperature, min.             | -40 °C |
| Storage temperature, max.             | 70 °C                          | Operating temperature, min.           | -50 °C |
| Operating temperature, max.           | 130 °C                         | Temperature range, installation, min. | -25 °C |
| Temperature range, installation, max. | 130 °C                         |                                       |        |

## Rated data acc. to IEC

|                                                                           |                        |                                                                       |                   |
|---------------------------------------------------------------------------|------------------------|-----------------------------------------------------------------------|-------------------|
| tested acc. to standard                                                   | IEC 60664-1, IEC 61984 | Rated current, min. number of poles (Tu=20°C)                         | 57 A              |
| Rated current, max. number of poles (Tu=20°C)                             | 41 A                   | Rated current, min. number of poles (Tu=40°C)                         | 41 A              |
| Rated current, max. number of poles (Tu=40°C)                             | 41 A                   | Rated voltage for surge voltage class / pollution degree II/2         | 1,000 V           |
| Rated voltage for surge voltage class / pollution degree III/2            | 630 V                  | Rated voltage for surge voltage class / pollution degree III/3        | 630 V             |
| Rated impulse voltage for surge voltage class/ pollution degree II/2      | 6 kV                   | Rated impulse voltage for surge voltage class/ pollution degree III/2 | 6 kV              |
| Rated impulse voltage for surge voltage class/ contamination degree III/3 | 6 kV                   | Short-time withstand current resistance                               | 3 x 1s with 420 A |
| Clearance, min.                                                           | 6.9 mm                 | Creepage distance, min.                                               | 9.6 mm            |

## SV 7.62HP/04/270MF3 3.5SN BK BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Rated data acc. to CSA

Institute (CSA)



Certificate No. (CSA)

200039-1121690

|                                   |                                                                        |
|-----------------------------------|------------------------------------------------------------------------|
| Rated voltage (Use group B / CSA) | 300 V                                                                  |
| Rated voltage (Use group D / CSA) | 600 V                                                                  |
| Rated current (Use group C / CSA) | 35 A                                                                   |
| Reference to approval values      | Specifications are maximum values, details - see approval certificate. |

|                                   |       |
|-----------------------------------|-------|
| Rated voltage (Use group C / CSA) | 300 V |
| Rated current (Use group B / CSA) | 35 A  |
| Rated current (Use group D / CSA) | 5 A   |

## Rated data acc. to UL 1059

Institute (cURus)



Certificate No. (cURus)

E60693

|                                       |                                                                        |
|---------------------------------------|------------------------------------------------------------------------|
| Rated voltage (Use group B / UL 1059) | 300 V                                                                  |
| Rated voltage (Use group D / UL 1059) | 600 V                                                                  |
| Rated current (Use group C / UL 1059) | 40.5 A                                                                 |
| Clearance distance, min.              | 6.9 mm                                                                 |
| Reference to approval values          | Specifications are maximum values, details - see approval certificate. |

|                                       |        |
|---------------------------------------|--------|
| Rated voltage (Use group C / UL 1059) | 300 V  |
| Rated current (Use group B / UL 1059) | 40.5 A |
| Rated current (Use group D / UL 1059) | 5 A    |
| Creepage distance, min.               | 9.6 mm |

## Packing

|           |        |            |        |
|-----------|--------|------------|--------|
| Packaging | Box    | VPE length | 338 mm |
| VPE width | 130 mm | VPE height | 33 mm  |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002637    | ETIM 7.0    | EC002637    |
| ETIM 8.0    | EC002637    | ECLASS 9.0  | 27-44-04-02 |
| ECLASS 9.1  | 27-44-04-02 | ECLASS 10.0 | 27-44-04-02 |
| ECLASS 11.0 | 27-46-02-01 | ECLASS 12.0 | 27-46-02-01 |

## Important note

|                |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |
|----------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| IPC conformity | Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.                                                                                                                                                                                     |
| Notes          | <ul style="list-style-type: none"> <li>• Additional variants on request</li> <li>• Rated current related to rated cross-section &amp; min. No. of poles.</li> <li>• P on drawing = pitch</li> <li>• Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.</li> <li>• Long term storage of the product with average temperature of 50 °C and average humidity 70%, 36 months</li> </ul> |

**SV 7.62HP/04/270MF3 3.5SN BK BX****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Approvals**

Approvals



ROHS Conform

UL File Number Search UL Website

Certificate No. (cURus) E60693

**Downloads**

|                                             |                                                                                                                                                                                                                                                                                                                                                                                                               |
|---------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Approval/Certificate/Document of Conformity | <a href="#">Declaration of the Manufacturer</a>                                                                                                                                                                                                                                                                                                                                                               |
| Engineering Data                            | <a href="#">CAD data – STEP</a>                                                                                                                                                                                                                                                                                                                                                                               |
| Engineering Data                            | <a href="#">EPLAN, WSCAD</a>                                                                                                                                                                                                                                                                                                                                                                                  |
| Catalogues                                  | <a href="#">Catalogues in PDF-format</a>                                                                                                                                                                                                                                                                                                                                                                      |
| Brochures                                   | <a href="#">FL DRIVES EN</a><br><a href="#">MB DEVICE MANUF. EN</a><br><a href="#">FL DRIVES DE</a><br><a href="#">FL HEATING ELECTR EN</a><br><a href="#">FL APPL. INVERTER EN</a><br><a href="#">FL BASE STATION EN</a><br><a href="#">FL ELEVATOR EN</a><br><a href="#">FL POWER SUPPLY EN</a><br><a href="#">FL 72H SAMPLE SER EN</a><br><a href="#">PO OMNIMATE EN</a><br><a href="#">PO OMNIMATE EN</a> |


## SV 7.62HP/04/270MF3 3.5SN BK BX

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings







## Dimensional drawing



## Connection diagram

|                |                                  |                                                                                     |   |   |   |   |   |   |
|----------------|----------------------------------|-------------------------------------------------------------------------------------|---|---|---|---|---|---|
| 6              | M(S)F6                           | o                                                                                   | o | o | o | o | X | o |
| 6              | M(S)F5                           | o                                                                                   | o | o | o | X | o | o |
| 6              | M(S)F4                           | o                                                                                   | o | o | X | o | o | o |
| 6              | M(S)F3                           | o                                                                                   | o | X | o | o | o | o |
| 6              | M(S)F2                           | o                                                                                   | X | o | o | o | o | o |
| 5              | M(S)F5                           | o                                                                                   | o | o | o | X | o |   |
| 5              | M(S)F4                           | o                                                                                   | o | o | X | o | o |   |
| 5              | M(S)F3                           | o                                                                                   | o | X | o | o | o |   |
| 5              | M(S)F2                           | o                                                                                   | X | o | o | o | o |   |
| 4              | M(S)F4                           | o                                                                                   | o | o | X | o |   |   |
| 4              | M(S)F3                           | o                                                                                   | o | X | o | o |   |   |
| 4              | M(S)F2                           | o                                                                                   | X | o | o | o |   |   |
| 3              | M(S)F3                           | o                                                                                   | o | X | o |   |   |   |
| 3              | M(S)F2                           | o                                                                                   | X | o | o |   |   |   |
| 2              | M(S)F2                           | o                                                                                   | X | o |   |   |   |   |
| NO OF<br>POLES | X = MIDDLE<br>FLANGE<br>POSITION | 1                                                                                   | 2 | 3 | 4 | 5 | 6 | 7 |
|                |                                  |  |   |   |   |   |   |   |

SHOWN: SV 7.62HP/04/90MSF





$D = \varnothing 1.3$   
 $d = 0.8 \times 1.0$

|                          |                          |             |            |              |             |       |      |   |    |    |    |    |    |  |  |
|--------------------------|--------------------------|-------------|------------|--------------|-------------|-------|------|---|----|----|----|----|----|--|--|
| W                        | SV 7.62HP/08/...M(S/L)F5 | 8           | 60.92      | 2.34         |             |       |      |   | MF |    |    |    |    |  |  |
|                          | SV 7.62HP/06/...M(S/L)F6 |             |            |              |             |       |      |   |    |    | MF |    |    |  |  |
|                          | SV 7.62HP/06/...M(S/L)F5 |             |            |              |             |       |      |   |    |    | MF |    |    |  |  |
|                          | SV 7.62HP/06/...M(S/L)F4 |             |            |              | 6           | 45.72 | 1.80 |   |    |    |    | MF |    |  |  |
|                          | SV 7.62HP/06/...M(S/L)F3 |             |            |              |             |       |      |   |    |    | MF |    |    |  |  |
|                          | SV 7.62HP/06/...M(S/L)F2 |             |            | MF           |             |       |      |   |    |    |    |    |    |  |  |
|                          | SV 7.62HP/05/...M(S/L)F5 | 5           | 38.10      | 1.50         |             |       |      |   |    |    |    |    | MF |  |  |
|                          | SV 7.62HP/05/...M(S/L)F4 |             |            |              |             |       |      |   |    | MF |    |    |    |  |  |
|                          | SV 7.62HP/05/...M(S/L)F3 |             |            |              |             |       |      |   |    | MF |    |    |    |  |  |
|                          | SV 7.62HP/05/...M(S/L)F2 |             |            |              |             |       | MF   |   |    |    |    |    |    |  |  |
|                          | SV 7.62HP/04/...M(S/L)F4 | 4           | 30.48      | 1.20         |             |       |      |   |    | MF |    |    |    |  |  |
|                          | SV 7.62HP/04/...M(S/L)F3 |             |            |              |             |       |      |   |    | MF |    |    |    |  |  |
|                          | SV 7.62HP/04/...M(S/L)F2 |             |            |              |             |       | MF   |   |    |    |    |    |    |  |  |
|                          | SV 7.62HP/03/...M(S/L)F3 | 3           | 22.86      | 0.90         |             |       |      |   |    | MF |    |    |    |  |  |
|                          | SV 7.62HP/03/...M(S/L)F2 |             |            |              |             |       |      |   |    | MF |    |    |    |  |  |
| SV 7.62HP/02/...M(S/L)F2 | 2                        | 15.24       | 0.60       |              |             |       |      |   | MF |    |    |    |    |  |  |
| description              | n                        | no of poles | L1<br>[mm] | L1<br>[inch] | 1           | 2     | 3    | 4 | 5  | 6  | 7  | 8  |    |  |  |
|                          |                          |             |            |              | position MF |       |      |   |    |    |    |    |    |  |  |

For the mounting of PCBs, it should be noted that the rated data relates only to the PCB components alone.  
The necessary creepage and clearance paths must be observed in connection with the respective applicant in accordance to IEC 664 / VDE 0110.  
The current-carrying capacity and pitch tolerance is to be determined according to DIN IEC 326 part 3 very fine.

Weidmüller PCB components are tested to the DIN EN 61984 standard, and are valid for its field of application. Provided that the components are used to the intended purpose, all requirements with respect to the occurring of electrical, mechanical, thermic and corrosive stress will be satisfied.



|                           |                        |
|---------------------------|------------------------|
| 3.5                       | +0.1                   |
|                           | -0.3                   |
| Stiftlänge/<br>pin length | Toleranz/<br>tolerance |

GENERAL TOLERANCE:  
DIN ISO 2768-m



Scale: 2:1

Supersedes: .

|                               |  |                     |  |                                                                                                                                                                                                                                                     |  |
|-------------------------------|--|---------------------|--|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|
|                               |  |                     |  | Cat.no.: .                                                                                                                                                                                                                                          |  |
| 100459/5<br>12.06.18 HELIS_MA |  | 00                  |  | <div><div><div><div><div><div></div><div><b>Weidmüller</b></div><div></div></div><div></div></div></div><div><div>3 49530</div><div>19</div></div></div></div> |  |
| Modification                  |  |                     |  | Drawing no. _____ Issue _____                                                                                                                                                                                                                       |  |
|                               |  |                     |  | Sheet 01 of 01 sheet                                                                                                                                                                                                                                |  |
| Date                          |  | Name                |  | <div><div><div><div><div></div><div><b>SV 7.62HP...M(S/L)F...</b></div><div></div></div><div><div>STIFTLEISTE</div><div>MALE HEADER</div></div></div></div><div>Product file: SV/BVZ 7.62HP</div><div>734</div></div>                               |  |
| Drawn                         |  | 24.02.2009 HELIS_MA |  |                                                                                                                                                                                                                                                     |  |
| Responsible                   |  | KRUG_M              |  |                                                                                                                                                                                                                                                     |  |
| Checked                       |  | 10.07.2018 HERTEL_S |  |                                                                                                                                                                                                                                                     |  |
| Approved                      |  | LANG_T              |  |                                                                                                                                                                                                                                                     |  |

**SV 7.62HP...M(S/L)F...**  
STIFTFLEISTE  
MALE HEADER

Product file: SV/BVZ 7.62HP

7340


## Recommended wave soldering profiles

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

### Single Wave:



### Double Wave:



### Wave soldering profiles

Wired connection elements should be processed in accordance with the DIN EN 61760-1 standard. We have included two recommendations for practical wave soldering profiles, with which Weidmüller PCB terminals and connectors are qualified.

When choosing a suitable profile for your application, the following factors also need to be considered:

- PCB thickness
- Proportion of Cu in the layers
- Single/double-sided assembly
- Product range
- Heating and cooling rates

The single and double wave profiles each indicate the recommended operating range, including the maximum soldering temperature of 260 °C. In practice, the maximum soldering temperature is quite often well below the above maximum profile.

We reserve the right to make technical changes.