

















TYPE 1




TYPE II



NOTES	
1	NOT DIMENSIONED GEOMETRY HAS TO BE TAKEN FROM THE CORRESPONDING 3D DATA FILE
2	MATERIAL SPECIFICATION: SILICONE, AUTOLUBRICATION
3	TENSILE STRENGTH : RM MIN 6.2 N/MM ²
4	ELONGATION : 375% DIN 53504-S2
5	DURUMETER ORIGINAL: SHORE(A) 50±5 DIN53505
6	MEASURE ON TEST SLABS

SCALE
2:1



DWG PART		DISTR CO
PART DRAWING		
WEIGHT (GRI)	D	
VOLUME (CM ³)		
ROUTING		

UNLESS OTHERWISE SPECIFIED

GENERAL TOLERANCES
ACCORDING TO:
SEE CHART

GD&T

ISO 1101

REFERENCE
ORIGINAL DESIGN
6501.920/K

FIRST ANGLE PROJECTION

DO NOT SCALE

USE MATH DATA

• **A P T I V** •

CONNECTION SYSTEMS

Chennai, India

THIS DRAWING IS THE PROPERTY OF ACTIV AND CONTAINS ACTIV
CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION OR
UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA, AS
AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS
AUTHORIZATION, IS PROHIBITED.

	DATE
DR SURESHKUMAR R	21SE2
ARVD1 THOMAS R	21SE2

APVD1	THOMAS B	21SE2
APVD2	THOMAS B	21SE2
APVD3		

APVD4	
APVD5	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER A	

MATERIAL	10949001
SEE TABLE	

DRAWING NAME
SINGLE WIRE SEAL

DRAWING NUMBER
1 26 88485

SIZE	SCALE	FRAME NO	SHEET NO	STG	REV
A0	10:1	1 OF 1	1 OF 1	B	01

10	10.1	10.1	10.1	10.1	10.1
2			1		

SHARP CORNER TOLERANCE

	DIMENSIONAL RANGE (MM)					CHART
FROM	> 0	> 25	> 60	> 80	> 80	
TO	25	60	80			

TOLERANCE UNLESS OTHERWISE SPECIFIED

	> 0.3	> 0.5	> 0.6	> 0.7
ANGULAR TOLERANCE	12°			

DO NOT SCALE

USE MATH DATA	U	NX
---------------	---	----