

FEATURES

- Winding type realizes small size and low profile
- Prevention of common mode noise at high frequency
- Excellent solderability
- Operating temperature -40~+125℃ (Including self - temperature rise)



APPLICATIONS

- USB2.0 of PC, peripheral equipments, small digital AV equipments, etc.
- LVDS lines of Note PC, LCD
- Audio lines


PRODUCT IDENTIFICATION

WCM 3225 N- 2 - 501 T F

① ② ③ ④ ⑤ ⑥ ⑦



- ① Series Name:Wire Wound Chip Common Mode Filters
- ② Dimensions
- ③ Category:
- ④ Number of Lines 2P=2 lines
- ⑤ Common Mode Impedance(Ω): 501 = 500 Ω
- ⑥ Packing: Tape & Reel
- ⑦ F:Hazardous Substance Free Products

Shapes and Dimensions [Dimensions in mm]



Series:	WCM3225NF-2-Series
A(mm)	3.2±0.2
B(mm)	2.5.±0.2
C(mm)	2.2±0.2
D1(mm)	0.80±0.1
D2(mm)	0.90±0.1
G1(mm)	1.9
G2(mm)	0.75
H(mm)	2.55
L(mm)	3.7

Equivalent Circuit / Materials




NO.	Description	Specification
a	Upper Plate	Ferrite
b	Core	Ferrite Core
c	Termination	Ag/Ni/Sn
d	Wire	Enameled Copper Wire

Electrical Characterisitics:


Part No.	Common mode Impedance (Ω)	DC Resistance Max.(Ω)	Test Frequency (MHz)	Rated Volt. (Vdc)	Irms (mA)max.	IR (MΩ) min.
WCM3225N-2-800TF	80±25%	0.12	100	50	640	10
WCM3225N-2-161TF	160±25%	0.15	100	50	480	10
WCM3225N-2-271TF	270±25%	0.25	100	50	450	10
WCM3225N-2-501TF	500±25%	0.30	100	50	1000	10
WCM3225N-2-601TF	600±25%	0.20	100	50	1000	10
WCM3225N-2-801TF	800±25%	0.35	100	50	350	10
WCM3225N-2-102TF	1000±25%	0.35	100	50	480	10

MEASURING CIRCUITS 2LINE

Common mode




Differential mode




Curve Frequency (MHz)


WCM3225N-2-800TF




WCM3225N-2-161TF




WCM3225N-2-271TF




WCM3225N-2-501TF




WCM3225N-2-601TF



WCM3225N-2-801TF




WCM3225N-2-102TF



Reliability and Test Condition

Item	Performance	Test Condition
Operating temperature	-40~+125℃ (Including self - temperature rise)	
Storage temperature	-40~+125℃ (on board)	
Electrical Performance Test		
Impedance	Refer to standard electrical characteristics list.	Keysight E4991B + Keysight 16197A
DCR		Agilent-34420A Agilent-4338B
Insulation Resistance	Test Voltage : Rated Voltage Time : 1 minute max.	Chroma 19073
Temperature Rise Test	Rated Current ΔT 40℃ Max	1.Applied the allowed DC current. 2.Temperature measured by digital surface thermometer
Reliability Test		
Life Test	Appearance : No damage. Impedance : within \pm 15% of initial value DCR : within \pm 15% of initial value and shall not exceed the specification value	Preconditioning: Run through reflow for 3 times. (IPC/JEDECJ-STD-020F Classification Reflow Profiles) Temperature : 85 \pm 2℃ Applied current : rated current Duration : 1000 \pm 12hrs Measured at room temperature after placing for 24 hrs.
Load Humidity		Preconditioning: Run through reflow for 3 times. (IPC/JEDECJ-STD-020F Classification Reflow Profiles) Humidity : 85 \pm 3% RH Temperature : 85℃ \pm 2℃ Duration : 1000hrs Min. Bead : with 100% rated current Inductance : with 10% rated current Measured at room temperature after placing for 24 hrs.
Moisture Resistance		Preconditioning: Run through reflow for 3 times. (IPC/JEDEC J-STD-020F Classification Reflow Profiles) 1. Baked at 50℃ for 25hrs, measured at room temperature after placing for 4 hrs. 2. Raise temperature to 65 \pm 2℃ 90-100%RH in 2.5hrs, and keep 3 hours, cool down to 25℃ in 2.5hrs. 3. Raise temperature to 65 \pm 2℃ 90-100%RH in 2.5hrs, and keep 3 hours, cool down to 25℃ in 2.5hrs, keep at 25℃ for 2hrs then keep at -10℃ for 3hrs. 4. Keep at 25℃ 80-100%RH for 15min and vibrate at the frequency of 10 to 55 Hz to 10 Hz, measured at room temperature after placing for 1~2 hrs.
Thermal Shock		Preconditioning: Run through reflow for 3 times. (IPC/JEDEC J-STD-020F Classification Reflow Profiles) Condition for 1 cycle Step1 : -40 \pm 2℃ 30 \pm 5min Step2 : 85 \pm 2℃ \leq 0.5min Step3 : 85 \pm 2℃ 30 \pm 5min Number of cycles : 500 Measured at room temperature after placing for 24 hrs.
Vibration		Preconditioning: Run through reflow for 3 times. (IPC/JEDEC J-STD-020F Classification Reflow Profiles) Oscillation Frequency : 10Hz~2kHz~10Hz for 20 minutes Equipment : Vibration checker Total Amplitude :10g Testing Time : 12 hours (20 minutes, 12 cycles each of 3 orientations)

Item	Performance	Test Condition														
Bending	Appearance : No damage. Impedance : within±15% of initial value DCR : within±15% of initial value and shall not exceed the specification value	Shall be mounted on a FR4 substrate of the following dimensions: >=0805 inch(2012mm):40x100x1.2mm <0805 inch(2012mm):40x100x0.8mm Bending depth: >=0805 inch(2012mm):1.2mm <0805 inch(2012mm):0.8mm duration of 10 sec.														
Shock		<table><tr><th>Type</th><th>Peak value (g's)</th><th>Normal duration (D) (ms)</th><th>Wave form</th><th>Velocity change (V)ft/sec</th></tr><tr><td>SMD</td><td>50</td><td>11</td><td>Half-sine</td><td>11.3</td></tr><tr><td>Lead</td><td>50</td><td>11</td><td>Half-sine</td><td>11.3</td></tr></table> 3 shocks in each direction along 3 perpendicular axes. (18 shocks).	Type	Peak value (g's)	Normal duration (D) (ms)	Wave form	Velocity change (V)ft/sec	SMD	50	11	Half-sine	11.3	Lead	50	11	Half-sine
Type	Peak value (g's)	Normal duration (D) (ms)	Wave form	Velocity change (V)ft/sec												
SMD	50	11	Half-sine	11.3												
Lead	50	11	Half-sine	11.3												
Solderability	More than 95% of the terminal electrode should be covered with solder	a. Method B, 4hrs @155°C dry heat @235°C±5°C Testing Time : 5 +0/-0.5 seconds b. Method D category 3. (8hours ± 15 min)@ 260°C±5°C Testing Time : 30 +0/-0.5 seconds														
Resistance to Soldering Heat	Appearance : No damage. Impedance : within±15% of initial value DCR : within±15% of initial value and shall not exceed the specification value	Depth: completely cover the termination <table><tr><th>Temperature(°C)</th><th>Time(s)</th><th>Temperature ramp/immersion and emersion rate</th><th>Number of heat cycles</th></tr><tr><td>260 ±5 (solder temp)</td><td>10 ±1</td><td>25mm/s ±6 mm/s</td><td>1</td></tr></table>	Temperature(°C)	Time(s)	Temperature ramp/immersion and emersion rate	Number of heat cycles	260 ±5 (solder temp)	10 ±1	25mm/s ±6 mm/s	1						
Temperature(°C)		Time(s)	Temperature ramp/immersion and emersion rate	Number of heat cycles												
260 ±5 (solder temp)	10 ±1	25mm/s ±6 mm/s	1													
Terminal Strength		Preconditioning: Run through reflow for 3 times. (IPC/JEDEC J-STD-020F Classification Reflow Profiles) With the component mounted on a PCB with the device to be tested, apply a force (>0805:1kg, <=0805:0.5kg) to the side of a device being tested. This force shall be applied for 60 +1 seconds. Also the force shall be applied gradually as not to apply a shock to the component being tested. 														

Soldering and Mounting

1. Soldering

Mildly activated rosin fluxes are preferred. Magnetsys terminations are suitable for re-flow soldering systems. If hand soldering cannot be avoided, the preferred technique is the utilization of hot air soldering tools.

1.1 Soldering Reflow:


Recommended temperature profiles for lead free re-flow soldering in Figure 1. Table 1.1&1.2 (J-STD-020F)

1.2 Soldering Iron:

Products attachment with a soldering iron is discouraged due to the inherent process control limitations. In the event that a soldering iron must be employed the following precautions are recommended. (Figure 2.)

- Preheat circuit and products to 150°C
- Never contact the ceramic with the iron tip
- Use a 20 watt soldering iron with tip diameter of 1.0mm
- 350°C tip temperature (max)
- 1.0mm tip diameter (max)
- Limit soldering time to 4~5sec.

Fig.1 Soldering Reflow



Reflow times: 3 times max

Fig.2 Iron soldering temperature profiles




Table (1.1): Reflow Profiles

Profile Type:	Pb-Free Assembly
Preheat	
-Temperature Min(T_{smin})	150°C
-Temperature Max(T_{smax})	200°C
-Time(t_s)from(T_{smin} to T_{smax})	60-120seconds
Ramp-up rate(T_L to T_p)	°C/second max.
Liquidus temperature(T_L)	217°C
Time(t_L)maintained above T_L	60-150 seconds
Classification temperature(T_c)	See Table (1.2)
Time(t_p) at $T_c - 5^\circ\text{C}$ (T_p should be equal to or less than T_c .)	< 30 seconds
Ramp-down rate(T_p to T_L)	6°C /second max.
Time 25°C to peak temperature	8 minutes max.

T_p : maximum peak package body temperature, T_c : the classification temperature.

For user (customer) T_p should be equal to or less than T_c .


Table (1.2) Package Thickness/Volume and Classification Temperature (T_c)

	Package Thickness	Volume mm ³ <350	Volume mm ³ 350-2000	Volume mm ³ >2000
PB-Free Assembly	<1.6mm	°C	260°C	260°C
	1.6-2.5mm	260°C	250°C	245°C
	≥2.5mm	250°C	245°C	245°C

Reflow is referred to standard IPC/JEDEC J-STD-020F


Packaging

(1) Tape Dimensions(Unit:mm)



Size	Ao(mm)	Bo(mm)	Ko(mm)	W(mm)	E(mm)	F(mm)	Po(mm)	P1(mm)	Do(mm)
WCM3225N	2.8±0.10	3.5±0.10	2.65±0.10	12.0±0.10	1.75±0.10	5.50±0.1	4.0±0.05	8.0±0.10	1.5±0.05

(2) Reel



Type	A(mm)	B(mm)	C(mm)	D(mm)
7"x12mm	13.5±0.5	60.0±2	13.5±0.5	178.0±2

Part No.	Tape	MPQ
WCM3225N-2-*	Embossed Tape	2000 Pcs