





RoHS



NOTE:  
1.Rating: 50V 100mA DC  
2.Insulation Resistance:≥100 MΩ  
3.Withstand voltage:AC 500V 1Minute  
4.Operating Force Range: 1000gf Max  
5.Mechanical Life:3,000 Cycles

|     |                |        |     |                 |              |
|-----|----------------|--------|-----|-----------------|--------------|
| ⑥   | Dust film      |        | 1   | Polyimide tape  |              |
| ⑤   | Terminal       |        | 2   | Phosphor bronze | Gold plating |
| ④   | Contact spring |        | 1   | Phosphor bronze | Gold plating |
| ③   | Handle         |        | 1   | PA46            | White        |
| ②   | Cover          |        | 1   | PPS             | Black        |
| ①   | Base           |        | 1   | PPS             | Black        |
| NO. | Name           | Number | Qty | Materil         | Remarks      |

YUANDI® Yuandi Electronics Co.,Ltd

|          |      |       |            |
|----------|------|-------|------------|
| design   | date | name  | DIP SWITCH |
| Review   | date | model | TP-01      |
| Approved | date |       |            |

Drawing number: A4

modify Review Approved

|       |       |
|-------|-------|
| angle | ±2°   |
| 10~30 | ±0.30 |
| 5~10  | ±0.20 |
| ~ 5   | ±0.10 |

Tolerance not specified

Proportion

1:1

unit

mm

gaps number

A4