




SPECIFICATIONS

Current Rating: 1.5 Amps
 Insulation Resistance: 1000M Ω Min
 Contact Resistance: 20m Ω Max
 Withstanding Voltage: AC 500V
 Operation Temperature: -40° to +105°
 Contact Material: Brass
 Standard: PA6T
 Insulator Material: Polyester (UL 94V-0)
 Contact Plating: Gold Flash
 Max. Processing Temp: 240°C for 30-60 seconds (260°C for 5 seconds)


P/N	PIN	DIM.A	DIM.B
FH2.0-02-01PWS-R	1	0.00	2.00
FH2.0-02-02PWS-R	2	2.00	4.00
FH2.0-02-03PWS-R	3	4.00	6.00
FH2.0-02-04PWS-R	4	6.00	8.00
FH2.0-02-05PWS-R	5	8.00	10.00
FH2.0-02-06PWS-R	6	10.00	12.00
FH2.0-02-07PWS-R	7	12.00	14.00
FH2.0-02-08PWS-R	8	14.00	16.00
FH2.0-02-09PWS-R	9	16.00	18.00
.....
FH2.0-02-40PWS-R	40	(PIN-1)x2.0	(PIN)x2.0



RECOMMEND P.C.B LAYOUT
 PCB TOLERANCE: ±0.05 (TOP VIEW)

PART NUMBER DESCRIPTION:

FH2.0-02-NPWS-R



MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: 2.0FH H4.3 2xnPin SMT W4.5 U型 PC6.5 PB4.6 6T
DECIMALS:	ANGLES:		PAR FH2.0-02-NPWS-R
X.±0.30	X°±5'		DWN
X.X±0.20	X.X'±1"		CHKD
X.XX±0.10	X.XX'±0.5"	APVD	SCALE N:A UNIT:MM
CUSTOMER COPY		SIZE:A4	SHEET:1F1 REV:A