








SPECIFICATION


- 1.Rating : DC 50V 0.5A.
- 2.Function: 2P2T
- 3.Contact resistance: $\leq 100\text{m}\Omega$.
- 4.Insulation resistance: $\geq 100\text{M}\Omega$ (DC500V).
- 5.Withstanding voltage: 500VAC .
- 6.Operating Force: $350\pm 100\text{gf}$.
- 7.life test: 10,000 cycles.
- 8.Operation temperature range: -25°C ~ 85°C .
- 9.Sign"* "is importance dimension.



SCHEMATIC (NON-SHORTING)

P.C.B LAYOUT
BOTTOM VIEW

10	SLEEVE	ABS	1														
9	CONTACT CLIP	PHOSPHOR BRONZE	2	Ag CLAD													
8	TERMINAL	BRASS	6	Ag PLATED	TOLERANCE UNLESS SPECIFIED												
7	BASE	PHENOLIC RESIN	1	NATURAL													
6	FRAME	STEEL	1	Ni PLATED	<1.5: ±0.1mm >1.5~5.0: ±0.25mm >5.0: ±0.3mm	ANGULAR ±1°							MLQ				
5	SPRING PLATE	PHOSPHOR BRONZE	1	NATURAL			NO	DATE	REVISIONS				BY	APPD			
4	CAM STICK	PHOSPHOR BRONZE	1	NATURAL	TITLE: PUSH SWITCH				UNIT : MM		ROHS	DWN					
3	SPRING	STEEL	1	Ni PLATED	MODEL: PS-12E05-S-L				SCALE: 1:1		COMPLIANT	CHK'D					
2	BLOCK	STEEL	1	Ni PLATED	 皓宇 HOOYA DONGGUANG HAUYU ELECTRONICS CO., LTD 东莞市弘皓电子有限公司										APPD		
1	KNOB	PA66	1														
NO.	PART NAME	MATERIAL	QTY	FINISHING													

PRO.AGL:		REV :A0
----------	---	---------