

SIGNAL ISOLATION SMT TRANSFORMERS

Ruggedized

PulseR
Ruggedized Solutions

X-1620

- R** Isolation Voltage: 3kVrms minimum
- R** Operating temperature: -55°C to +125°C
- R** Tin/Lead Construction
- R** Moisture Sensitivity Level: 3



Electrical Specifications @ 25°C

Part Number	Turns Ratio (Pri:Sec ±2%)	Primary Inductance (mH MIN)	DCR (Ω MAX)	Leakage Inductance (mH MAX)	C _{ww} (pF MAX)	C _d Pri @10MHz (pF MAX)	Primary Pins
X-1620	1CT:1CT	1	0.8	1.2	25	10	1-3

Mechanical

Schematic

X-1620



DIMENSIONS: $\frac{\text{Inches}}{\text{mm}}$

UNLESS OTHERWISE SPECIFIED ALL TOLERANCES ARE $\pm \frac{.010}{0.25}$

WEIGHT:-----1.16grams

TUBE:-----55/Tube

TAPE & REEL:-----400/Reel

For More Information **Corporate Headquarters**
PulseR, LLC

311 Sinclair Road
Bristol, PA 19007-6812
U.S.A

For Global Sales Representatives and
Locations Visit:

<http://www.pulseruggedized.com>

Tel: +1 215 781 6400

Fax: +1 215 781 6403

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright, 2019, PulseR, LLC. All rights reserved.