




RECOMMENDED PCB LAYOUT
FOR TOP ENTRYRECOMMENDED PCB LAYOUT
FOR BOTTOM ENTRY

SPECIFICATIONS 规格:

CURRENT RATING 电流额定值: 0.5 AMP
INSULATOR RESISTANCE 绝缘电阻值: 500 MEGOHMS MIN.
DIELECTRIC WITHSTANDING 耐电压: AC 200 V
CONTACT RESISTANCE 接触电阻值: 20mΩ Max.
OPERATING TEMPERATURE 工作温度: -40°C TO +105°C
CONTACT MATERIAL 端子物料: PHOSPHOR BRONZE
INSULATOR MATERIAL 绝缘体物料:
STANDARD 标准物料: POLYESTER 聚酯, LCP, UL 94-V0
SOLDERING PROCESS 可焊性:
LCP (STANDARD 标准物料) -


IR REFLOW 回流焊: 260°C for 10 sec.

WAVE 波峰焊: 250°C for 5-10 sec

MANUAL SOLDER 人工焊接: 350°C for 3-5 sec

MATES WITH 配套之母座 (SUBJECT TO PIN LENGTH 在端子长度适合的条件下):
BB080

By	AE	PN	SA	SA
DETAIL	DRAWING RELEASE	AMENDMENT TO PACKING OPTIONS, DIMENSION TABLE & NO. OF CONTACTS	AMENDMENT TO PLATING OPTIONS	CHANGES TO SPECIFICATION
REV DATE	A 18/09/09	B 28/09/09	C 22/12/09	D 30/12/09



CONTACTS	DIMENSIONS		
	A	B	C
6	1.60	2.66	0.80
8	2.40	3.46	1.60
10	3.20	4.26	2.40
12	4.00	5.06	3.20
14	4.80	5.86	4.00
16	5.60	6.66	4.80
18	6.40	7.46	5.60
20	7.20	8.26	6.40
22	8.00	9.06	7.20
24	8.80	9.86	8.00
26	9.60	10.66	8.80
28	10.40	11.46	9.60
30	11.20	12.26	10.40
32	12.00	13.06	11.20
34	12.80	13.86	12.00
36	13.60	14.66	12.80
38	14.40	15.46	13.60
40	15.20	16.26	14.40
42	16.00	17.06	15.20
44	16.80	17.86	16.00
46	17.60	18.66	16.80
48	18.40	19.46	17.60
50	19.20	20.26	18.40
52	20.00	21.06	19.20
54	20.80	21.86	20.00
56	21.60	22.66	20.80
58	22.40	23.46	21.60
60	23.20	24.26	22.40
62	24.00	25.06	23.20
64	24.80	25.86	24.00
66	25.60	26.66	24.80
68	26.40	27.46	25.60
70	27.20	28.26	26.40
72	28.00	29.06	27.20
74	28.80	29.86	28.00
76	29.60	30.66	28.80
78	30.40	31.46	29.60
80	31.20	32.26	30.40
82	32.00	33.06	31.20
84	32.80	33.86	32.00
86	33.60	34.66	32.80
88	34.40	35.46	33.60
90	35.20	36.26	34.40
92	36.00	37.06	35.20
94	36.80	37.86	36.00
96	37.60	38.66	36.80
98	38.40	39.46	37.60
100	39.20	40.26	38.40



Tolerances (Except as noted)	
Dimensions in mm	
X. ± 0.30	X.* ± 5.0°
X.X ± 0.25	X.X* ± 3.0°
X.XX ± 0.15	X.XX* ± 2.0°
X.XXX ± 0.10	X.XXX* ± 1.0°



Third Angle Projection

Part Number:-	Date:-
BB060	18 SEP 09
Description:-	
0.8mm x 1.2mm PITCH SOCKET, DUAL ROW, SURFACE MOUNT, VERTICAL, DUAL ENTRY	
THIS DRAWING IS CONFIDENTIAL AND MUST NOT BE COPIED OR DISCLOSED WITHOUT WRITTEN CONSENT	

Scale	Revision	Material	Drawn by	Sheet No.
NTS	D	See Note	ASE	E & OE 1/1

GCT

www.globalconnectortechology.com