







4. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



RECOMMENDED PCB LAYOUT
RECOMMENDED PCB THICKNESS:1.6mm
TOLERANCE: ± 0.05 (TOP VIEW)



OBSOLETE 	1.27um[50u"]	1775134-4
	0.76um[30u"]	1775134-3
	0.38um[15u"]	1775134-2
	0.15um[6u"]	1775134-1
	MIN. GOLD THICKNESS	PART NUMBER

CUSTOMER DRAWING

SEE NOTE

SEE NOTE

SEE NOTE

CUSTOMER DRAWING



TE Connectivity

MODULAR JACK, RJ45, SINGLE

RESTRICTED TO

	REV
--	-----

4	REV B
---	-------

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

- . - .

ALL RIGHTS RESERVED.



COPYRIGHT - By -

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

NOTE:

1. MATERIAL:

1.1 HOUSING: PA46, WITH 30% GF, UL94V-0, BLACK COLOR.

1.2 CONTACTS: PHOSPHOR BRONZE.

1.3 LED SOLDER TAIL: EPOXY, STEEL.

2. FINISH:

2.1 CONTACTS: (SEE TABLE) GOLD PLATED ON CONTACT AREA,
GOLD FLASH ON SOLDER TAIL,
1.27um [50u"] MIN. NICKEL UNDERPLATED OVERALL.








2.2 LED: 1.016um [40u"] COPPER UNDERPLATED OVERALL.


1.27um [50u"] NICKEL OVERALL.

1.27um [50u"] SILVER ON BONDING AREA.

2.032um [80u"] BRIGHT-TIN ON SOLDER AREA.

3. WAVE SOLDER CAPABLE TO 265°C PER TE SPEC 109-202, CONDITION B.

RECOMMENDED PCB LAYOUT
RECOMMENDED PCB THICKNESS: 1.6mm
TOLERANCE: ±0.05 (TOP VIEW)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN O. HU 22OCT2007		TE Connectivity									
		CHK S. HOU 22OCT2007											
DIMENSIONS: mm		APVD W.J. KE 22OCT2007		NAME MODULAR JACK, RJ45, SINGLE — —									
		PRODUCT SPEC 108-57535											
		APPLICATION SPEC —		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO			
MATERIAL SEE NOTE		FINISH SEE NOTE		WEIGHT —		A3		00779		C=1775134		—	
CUSTOMER DRAWING						SCALE 1:1		SHEET 3 OF 4		REV B			

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

- , - .

© COPYRIGHT - By -




ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

NOTES:

1. MATERIAL:
TRAY: PVC.
CARTON: CORRUGATED FIBER.
BOX: CORRUGATED FIBER.
2. DIMENSION: SEE DRAWING
3. QUANTITY: SEE TABLE
4. WEIGHT: SEE TABLE




DESICCATING AGENTS

BAG

CLAPBOARD


CLAPBOARD

BOX



8.26 KG	7.26 KG	100	25	2500	2-1775134-X
14.15 KG	12.15 KG				1-1775134-X
12.7 KG	10.7 KG	90		2250	1775134-X
GROSS WEIGHT	NET WEIGHT	PCS/TRAY	TRAY/BOX	PCS/BOX	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN O. HU 22OCT2007	 TE Connectivity		
		CHK S. HOU 22OCT2007			
		APVD W.J. KE 22OCT2007	NAME MODULAR JACK, RJ45, SINGLE		
		PRODUCT SPEC 108-57535			
		APPLICATION SPEC -	SIZE A3		
		WEIGHT 0			
		CUSTOMER DRAWING	CAGE CODE 00779		
			DRAWING NO 1775134		
			RESTRICTED TO -		
			SCALE 1:1		
			SHEET 4 OF 4		
			REV B		

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± - 1 PLC ± 0.3 2 PLC ± 0.2 3 PLC ± 0.15 4 PLC ± - ANGLES ± 3°
MATERIAL SEE NOTE	FINISH SEE NOTE