

MICRO SWITCH

A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY
FREDPORT, HAMMOND

SWITCH-BASIC

CATALOG LISTING
WZ-2RW84429-P52

AVJ5232

WZ-2RW84429-P52
PAGE 1 OF 1

DRAWING
NUMBER

ISSUE
8

REPLACES X68280-WZ

RELEASE NO. PR-7685

22AUG07

PSR

CHECK

17 FEB 06

RJ

CHECK

23 FEB 79

TSG

0033162

JA

22AUG07

CA

CHECK

16 FEB 79

GRT

16 FEB 79

16 FEB 79


16 FEB 79

16 FEB 79

16 FEB 79

16 FEB 79

16 FEB 79



NOTE
MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF .139 MAX DIA ON $1.000 \pm .002$ CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL
OPERATING FORCE — — — — — $3/4$ OZ MAX	CONTACT ARRANGEMENT S P N C	DO NOT SCALE PRINT
DIFFERENTIAL FORCE — — — — — $1/2$ OZ MAX	CODE L96 15A-125, 250 OR 480 VAC	UNLESS OTHERWISE SPECIFIED
PRETRAVEL — — — — — .625 MAX	$1/8$ HP-125 VAC; $1/4$ HP-250 VAC	DIMENSIONS ARE IN INCHES
DIFFERENTIAL TRAVEL — — — — — .027-.219	$1/2$ A-125 VDC; $1/4$ A-250 VDC	TOLERANCES ARE:
OVERTRAVEL — — — — — .140 MIN	-L288- -L306- -L315-	ONE PLACE (.0) $\pm .030$ TWO PLACE (.00) $\pm .015$ THREE PLACE (.000) $\pm .005$ ANGLES $\pm$
	CE 05 RU	WEIGHT
	16A 250V T85 5E4	

RASTER

O-50378

DRAWN