





Hexagonal head screw driver
P/N 61 03 600 0021
for hexagonal head screw
max. torque=0,5Nm



X=3
M3 x 16,8




X=0
4-40 UNC x 16,8



X=1
M3 x 17,6

X=2
4-40 UNC x 17,6

Internal grounding block
(optional)



1 For strain relief an additional InduCom cable clamp or a crimp flange and ferrule combination depending on the cable is necessary

Content InduCom hood			Spare parts (MOQ100)	
Pos.	Quantity	Description	Part Number	Quantity
01	1	metal hood		
02	1	metal cover		
03	2	blank piece (not assembled)	6103 000 0042	1
04	2	locking screw (assembled):		
		either knurled thumb screws 4-40 UNC (for 0118)	0967 002 9018	1
		or hexagonal M3 with captive washer (for 1118)	0967 002 9019	1
		or hexagonal 4-40 UNC with captive washer (for 2118)	0967 002 9020	1
		or knurled thumb screws M3 (for 3118)	0967 002 9017	1
05	1	grounding screw (not assembled) for version with internal grounding block	0963 002 0007	1
06	4	cover screw M2,5 with philips head (not losable in cover) max. torque=0,3Nm	0963 002 0006	1



All Dimensions in mm
Original Size DIN A3

Scale
1:1

Free size tol.

Ref.
Sub.



All rights reserved
Department EC PD - CN

Created by
ZENG

Inspected by
LUOK

Standardisation
HOFFMANN

Date
2018-03-08

State
Final Release

Title
InduCom size 4 (37-pole) easy access hood assembly

Doc-Key / ECM-Nr.
100522752/UGD/000/E
500000132046

Type
TB

Number
6103001X118

Rev.
E

Page
1/1

E 6103 001 X118 YYY

6103 001 0118	4-40 UNC	Knurled thumb screw	Without ring	With internal grounding block
6103 001 1118	M3	Hexagonal screw with captive washer	1	
6103 001 2118	4-40 UNC	Hexagonal screw with captive washer	3	
6103 001 3118	M3	Knurled thumb screw	With ring	Without internal grounding block
6103 001 0118 010	4-40 UNC	Knurled thumb screw	Without ring	
6103 001 1118 010	M3	Hexagonal screw with captive washer	1	
6103 001 2118 010	4-40 UNC	Hexagonal screw with captive washer	3	
6103 001 3118 010	M3	Knurled thumb screw	With ring	
Part Number	Dim. B screw size	Screw type	Identification for locking screw	Internal grounding block