







LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
A1	-		A	NEW DWG.	29FEB2000	DJ	GM
			B	UPDATE	24 JUL2001	KR	DJ
			B1	UPDATE	26MAY2008	Haas	Pfeil



2:1

REMARKS
Bemerkungen

- 1 MATING PART ACC. TO TE-SPEC.: 114-18317
Gegenstecker nach
- 2 ONLY FOR FLK WIRE SEE DIN 72551
Nur fuer FLK-Leitungen nach
- 3 SURFACE: Oberflaeche:
-PRE TIN PLATED 1-3 μm -verzinnt 1-3 μm
-GOLD PLATED MIN. 0.8 μm -galv. vergoldet min. 0.8 μm
(ONLY CONTACT AREA) (nur Kontaktzone)
-SILVER PLATED 3-5 μm -galv. versilbert 3-5 μm
(ONLY CONTACT AREA) (nur Kontaktzone)
- 4 APPLICATION TOOLS OF CONTACTS SEE
APPLICATION SPEC.: 114-18269
Verarbeitungswerkzeuge der Kontakte siehe
Verarbeitungsspezifikation.: 114-18269
- 5 DETAILS OF DESIGN ARE UP TO THE MANUFACTURER
Einzelheiten der Ausfuehrung sind dem Hersteller ueberlassen
- 6 ONLY GERMAN LANGUAGE VERSION SHALL BE BINDING
Nur der Deutsche Text ist bindend



1-1355849-1	6-10 mm ²	CuNiSi	PRE TIN PLATED vorverzinnt	B
TE ORDER-NO. Bestell-Nr.	WIRE SIZE RANGE Leiterquerschnitt 	MATERIAL Werkstoff	SURFACE Oberfläche 	REV

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN 29FEB2000 Jakobeit.D.		 Tyco Electronics AMP GmbH 64625 Bensheim (Germany)	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME AMP MCP9.5 FLAT TYPE RECEPTACLE AMP MCP9.5 Buchsenkontakt; ASS'Y	
		0 PLC ±0.2 2 PLC ±- 3 PLC ±- 4 PLC ±0.0001 ANGLES ±			
MATERIAL		FINISH			
SEE TABLE		-			
		APVD 27MAY2008 Dfeilschifter.M. PRODUCT SPEC 108-18630 APPLICATION SPEC 114-18269		SIZE A2	
		WEIGHT -		CAGE CODE 00779	
		CUSTOMER DRAWING		DRAWING NO C-1355849	
				RESTRICTED TO -	
				SCALE 5:1 SHEET 1 of 1 REV B1	