

Features

- Uses Geener advanced MOS technology
- Extremely low on-resistance $R_{DS(on)}$
- Excellent $Q_g \times R_{DS(on)}$ product(FOM)
- Qualified according to JEDEC criteria

Applications

- Motor control and drive
- Battery management
- UPS (Uninterruptible Power Supplies)


Product Summary

V_{DS}	100V
$R_{DS(on)}$	3.5m
I_D	120A


100% DVDS Tested
100% Avalanche Tested



TOLL-8



TO-263



Package Marking and Ordering Information

Part #	Marking	Package	Packing	Reel Size	Tape Width	Qty
KCB032N10N	KCB032N10N	TO-263	Tape	N/A	N/A	1000pcs
KCT032N10N	KCT032N10N	TOLL	Tape	N/A	N/A	2000pcs

Absolute Maximum Ratings

Parameter	Symbol	Value	Unit
Drain-source voltage	V_{DS}	100	V
Continuous drain current $T_C=25^{\circ}\text{C}$ $T_A=25^{\circ}\text{C}$ $T_C=100^{\circ}\text{C}$	I_D	120 21 113	A
Pulsed drain current ($T_C = 25^{\circ}\text{C}$, t_p limited by T_{jmax})	$I_{D \text{ pulse}}$	480	A
Avalanche energy, single pulse ($L=0.5\text{mH}$, $R_g=25\Omega$)	E_{AS}	800	mJ
Gate-Source voltage	V_{GS}	± 20	V
Power dissipation ($T_C = 25^{\circ}\text{C}$)	P_{tot}	215	W
Operating junction and storage temperature	T_j, T_{stg}	-55...+150	$^{\circ}\text{C}$

Thermal Resistance

Parameter	Symbol	Max	Unit
Thermal resistance, junction – case.	R_{thJC}	0.58	°C/W
Thermal resistance, junction – ambient(min. footprint)	R_{thJA}	40	

Electrical Characteristic (at $T_j = 25\text{ }^{\circ}\text{C}$, unless otherwise specified)

Parameter	Symbol	Value			Unit	Test Condition
		min.	typ.	max.		

Static Characteristic

Drain-source breakdown voltage	BV_{DSS}	100	-	-	V	$V_{GS}=0V, I_D=250\mu A$
Gate threshold voltage	$V_{GS(th)}$	2.2	3	3.8	V	$V_{DS}=V_{GS}, I_D=250\mu A$
Zero gate voltage drain current	I_{DSS}	-	-	1	μA	$V_{DS}=100V, V_{GS}=0V$ $T_j=25^{\circ}\text{C}$ $T_j=125^{\circ}\text{C}$
Gate-source leakage current	I_{GSS}	-	-	± 100	nA	$V_{GS}=\pm 20V, V_{DS}=0V$
Drain-source on-state resistance	$R_{DS(on)}$	-	2.8 2.6	3.5 3.3	$m\Omega$	$V_{GS}=10V, I_D=50A$ TO-263 TOLL
Transconductance	g_{fs}	-	113	-	S	$V_{DS}=5V, I_D=50A$

Dynamic Characteristic

Input Capacitance	C_{iss}	-	7470	-	pF	$V_{GS}=0V, V_{DS}=50V,$ $f=1\text{MHz}$
Output Capacitance	C_{oss}	-	930	-		
Reverse Transfer Capacitance	C_{rss}	-	50	-		
Gate Total Charge	Q_G	-	130	-	nC	$V_{GS}=10V, V_{DS}=50V,$ $I_D=50A$
Gate-Source charge	Q_{gs}	-	35	-		
Gate-Drain charge	Q_{gd}	-	40	-		
Turn-on delay time	$t_{d(on)}$	-	50	-	ns	$V_{GS}=10V, V_{DS}=50V,$ $R_{GEN}=6\Omega, I_D=50A,$
Rise time	t_r	-	74	-		
Turn-off delay time	$t_{d(off)}$	-	97	-		
Fall time	t_f	-	30	-		
Gate resistance	R_G		1.5	Ω		$V_{GS}=0V, V_{DS}=0V, f=1\text{MHz}$

Body Diode Characteristic

Parameter	Symbol	Value			Unit	Test Condition
		min.	typ.	max.		
Body Diode Forward Voltage	V_{SD}	-	0.9	1.2	V	$V_{GS}=0V, I_{SD}=50A$
Body Diode Reverse Recovery Time	t_{rr}	-	68	-	ns	$V_{DS} = 50 V, I_F = 50A$ $di/dt = 100 A/\mu s$
Body Diode Reverse Recovery Charge	Q_{rr}	-	116	-	nC	

Electrical characteristics diagrams

Fig.1 Typ. transfer characteristics




Fig.2 Typ. output characteristics




Fig.3 Normalized on-resistance vs drain current




Fig.4 Typ. on-resistance vs gate-source voltage




Fig.5 Normalized on-resistance vs junction temperature




Fig.6 Typ. gate charge




Fig.7 Typ. forward characteristics of body diode




Fig.8 Safe operating area




Fig.9 Typ. Capacitance




Fig.10 Single pulse maximum power dissipation




Fig.11 Max. power dissipation vs case temperature




Fig.12 Max. continuous drain current vs case temperature




Fig.13 Normalized $V_{(BR)DSS}$ vs junction temperature




Fig.14 Normalized $V_{GS(th)}$ vs junction temperature






Fig.15 Transient thermal impedance from junction to case




Package Outline: TO-263



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	4.30	4.86	0.169	0.191
A1	0.00	0.25	0.000	0.010
A2	2.34	2.79	0.092	0.110
b	0.68	0.94	0.027	0.037
b2	1.15	1.35	0.045	0.053
c	0.33	0.65	0.013	0.026
c2	1.17	1.40	0.046	0.055
D	8.38	9.45	0.330	0.372
D1	6.90	8.17	0.272	0.322
e	2.54 BSC.		0.100 BSC.	
E	9.78	10.50	0.385	0.413
E1	6.50	8.60	0.256	0.339
H	14.61	15.88	0.575	0.625
L	2.24	3.00	0.088	0.118
L1	0.70	1.60	0.028	0.063
L2	1.00	1.78	0.039	0.070
L3	0.00	0.25	0.000	0.010

Package Outline: TOLL



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	2.15	2.45	0.085	0.096
b	0.60	0.90	0.024	0.035
b1	9.65	9.95	0.380	0.392
c	0.35	0.65	0.014	0.026
D	10.18	10.70	0.401	0.421
D1	3.15	3.45	0.124	0.136
E	9.70	10.10	0.382	0.398
E1	7.35	8.45	0.289	0.333
e	1.10	1.30	0.043	0.051
H	11.45	11.95	0.451	0.470
H1	6.55	7.50	0.258	0.295
L	1.35	2.10	0.053	0.083
L1	0.50	0.90	0.020	0.035
L2	0.40	0.80	0.016	0.031
L3	0.95	1.35	0.037	0.053